

Flexible Cable Management Raceway Spine Vertebrae, 3/4"(20mm)W x 1/2"(14mm)H - 20"(0.5m) length, Nylon 66 Network Cable/Power Cord Hider Kit, Wall Wire Duct System, UL Listed

**Product ID:** CBMFWD2014



This 20.6 in. (52.4 cm) flexible cable management spine/vertebrae raceway offers a flexible solution for neatly routing cables at your workstation to create a tidy and professional look.

This cable management raceway protects cables from damage while neatly routing them. The raceway is 0.6 in. (14 mm) x 0.8 in. (20 mm). Featuring individual loops that makes it easy to add, remove and organize cables within the raceway.

The built-in raceway connectors make it easy to create long cable runs by latching several raceways together. Each raceway features mating connectors at each end, enabling you customize the length of the raceway to meet your specific application.

The raceway features 0.5 in. (12.2 mm) x 0.2 in. (4.7 mm) mounting holes that enable you to easily mount the raceway to wood or drywall using screws (not included).

Made from durable Nylon 66 this network/power cable router/organizer is flexible and UL/94V-2 Rated.

This cable management raceway is TAA compliant and backed by a StarTech.com 2-year warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

## Certifications, Reports and Compatibility

## Applications

- Route cables at your workstation to create a tidy and professional look

## Features

- **PROFESSIONALLY ORGANIZE & ROUTE CABLES:** Cable management raceway protects cables from damage & neatly routes them in your office or server room; Features individual loops to add or remove cables
- **EXPANDABLE RACEWAY:** Create long cable runs by latching several units of this raceway with the built-in mating connectors at each end
- **TECHNICAL SPECIFICATIONS:** Length: 20.6" (52.4cm) Height: 0.6" (14mm) Total width: 0.8" (20mm) Flexible design Nylon 66 UL 94V-2 Rated RoHS
- **STARTECH.COM ADVANTAGE:** IT professional's choice for over 30 years; This surface mount cord cover kit/wiring duct system is backed for 2 years by StarTech.com, including free 24/5 tech support

---

### Performance

Warranty	2 Years
General Specifications	Special Features: Individual Cable Management Loops Mounting Hole Size: 0.48 in. [12.2 mm] x 0.19 in. [4.7 mm]

---

### Physical Characteristics

Color	Gray
Material	Nylon 66
Product Length	0.8 in [20.0 mm]
Product Width	19.7 in [50.0 cm]
Product Height	0.6 in [14.0 mm]
Weight of Product	0.7 oz [20.0 g]

---

### Packaging Information

Package Length	0.8 in [20.0 mm]
Package Width	19.7 in [50.0 cm]
Package Height	0.6 in [14.0 mm]
Shipping (Package) Weight	1.5 oz [41.7 g]

---

### What's in the Box

Included in Package	Raceway
---------------------	---------

---

***\*Product appearance and specifications are subject to change without notice.***

