

9"(22cm) Metal Cable Ties - 1/4"(7mm) wide, 2-1/4"(55mm) Bundle Dia. 100lb(45kg) Tensile Strength, Nylon Coated 316 Stainless Steel, Self Locking Metal Detectable Ties, 50 Pack

Product ID: CBMMCT



These stainless steel metal cable ties provide a strong solution to conveniently bundle and secure multiple cables, and to route and organize them. 50 cable ties are included, ensuring you'll have plenty on hand.

These stainless steel-cable ties are 9 in. (22 cm) in length securing cable bundles up to 2.16in (55mm) in diameter and up to 100 lbs. (45 kg) -- perfect for organizing network cables, power cables or other cables and wires.

Made of 316SS and Nylon 11 coated, these stainless steel ties are non-abrasive and weather, corrosion and impact resistant, making them suitable for any indoor or outdoor cable management solution, including marine applications. They're also metal detectable for use with fiber optic cables.

These stainless steel ties can easily be installed by hand. However, to reduce time and repetitive strain on your hands when installing many cable ties, StarTech.com also offers a Metal Cable Tie Tool (CBMMCTTOOL), that works with our cable ties as well as other metal cable ties (sold separately).

These cable wraps are TAA compliant and backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

- Route cables while mounting them to a wall or ceiling in your office or server room

Features

- **50-PACK OF DURABLE METAL ZIP TIES:** Stainless-steel cable ties made of 316SS are 9in (22 cm) long & 0.29in (7.6mm) wide, providing a strong solution to secure cable bundles up to 2.16in (55mm) in diameter
- **INDOOR & OUTDOOR USE:** Nylon 11 coated stainless-steel ties are non-abrasive and weather, corrosion and impact resistant; Suitable for indoor and outdoor cable management applications including marine
- **STRONG & VERSATILE:** Secure and route power & coax cable, RJ11 telephone wire, audio, video, RJ45 CAT5/CAT6 network & USB cables with these metal ties; Metal detectable for use with fiber optic cables
- **EASY INSTALLATION:** Ties can easily be installed by hand; A metal cable tie tool is available to reduce time and repetitive strain when installing many cable ties at once CBMMCTTOOL (sold separately)
- **STARTECH.COM ADVANTAGE:** IT professional's choice for over 30 years; These metal zip ties are backed for 2 years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Physical Characteristics

Warranty	2 Years
Color	Black
Material	316SS Stainless Steel
Product Length	8.9 in [22.5 cm]
Product Width	0.3 in [7.0 mm]
Product Height	0.0 in [0.3 mm]
Weight of Product	0.3 oz [8.2 g]

Packaging Information

Package Quantity	50
Package Length	13.6 in [34.5 cm]
Package Width	6.5 in [16.5 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	12.8 oz [364.0 g]

What's in the Box

Included in Package	50 - Steel Cable Ties
---------------------	-----------------------

****Product appearance and specifications are subject to change without notice.***