

100 Pack 8" Cable Ties - White Large Nylon/Plastic Zip Tie - Adjustable Electrical/Network Cable Wraps/-40 to +85C Temp/94V-2 Fire & UL Rated TAA

Product ID: CBMZT8N



These Large cable ties enable you to conveniently bundle and secure multiple cables, to route and organize them. 100 White cable ties are included, ensuring you'll have plenty on hand.

These plastic electrical cable wraps are 8" (203.2 mm) in length securing cable bundles up to 1.6" (40.6 mm) in diameter. They're quick and easy to install or remove, with adjustable tension and a basic one-piece design -- perfect for organizing network cables, power cables, or other cables at your home or office workstation.

Made of durable Nylon 66 material, these cable ties are tough and flexible. They've been rigorously tested to support up to 50 lbs 22.7 kg of weight & are UL94 V-2 fire rated, UL Approved, and CE & Lloyd's Register Certified.

To suit any application, StarTech.com offers a wide selection of these cable ties in different lengths and colors:

100 Pack - 4" (101.6 mm) Black Cable Ties (CBMZT4B)

100 Pack - 4" (101.6 mm) White Cable Ties (CBMZT4N)

1000 Pack - 4" (101.6 mm) Black Cable Ties (CBMZT4BK)

1000 Pack - 4" (101.6 mm) White Cable Ties (CBMZT4NK)

100 Pack - 6" (152.4 mm) Black Cable Ties (CBMZT6B)

100 Pack - 6" (152.4 mm) White Cable Ties (CBMZT6N)

1000 Pack - 6" (152.4 mm) Black Cable Ties (CBMZT6BK)

1000 Pack - 6" (152.4 mm) White Cable Ties (CBMZT6NK)

100 Pack - 8" (203.2 mm) Black Cable Ties (CBMZT8B)

100 Pack - 8" (203.2 mm) White Cable Ties (CBMZT8N)

1000 Pack - 8" (203.2 mm) Black Cable Ties (CBMZT8BK)

1000 Pack - 8" (203.2 mm) White Cable Ties (CBMZT8NK)

100 Pack - 10" (254 mm) Black Cable Ties (CBMZT10B)

100 Pack - 10" (254 mm) White Cable Ties (CBMZT10N)

1000 Pack - 10" (254 mm) Black Cable Ties (CBMZT10BK)

1000 Pack - 10" (254 mm) White Cable Ties (CBMZT10NK)

These cable wraps are backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

Features

- **100 PACK OF CABLE TIES:** Keep cables organized with 8" (203.2 mm) White zip ties for 1.6" 40 mm bundle diameter; Tool-less installation
- **INDUSTRIAL STRENGTH:** Made of durable Nylon 66 material, these tough, flexible, adjustable cable ties are tested to support up to 50 lbs 22.7 kg of weight & are UL94 V-2 fire rated
- **REDUCE CLUTTER:** Easy to install, tighten and see, these small plastic electrical cable wraps are ideal for reorganizing your workstation at home or office; StarTech.com Lifetime warranty
- **RELIABLE SAFETY:** 94V-2 Flammability Rating UL Approved CE Lloyd's Register Certified RoHS TAA Compliant
- **MULTI-LENGTH:** Available in 4" (254 mm) for 2.7" (68 mm) bundle 6" (152.4 mm) for 1.4" (36 mm) bundle 8" (203.2 mm) for 1.6" (40 mm) bundle 10" (254 mm) for 2.7" (68 mm) bundle Black or White

Physical Characteristics	Warranty	2 Years
	Color	White
	Material	Nylon 66
	Product Length	0.2 in [5 mm]
	Product Width	7.9 in [2 cm]
	Product Height	0.0 in [1 mm]
	Weight of Product	0.0 oz [1.25 g]

Packaging Information	Package Length	5.3 in [1.4 cm]
	Package Width	12.6 in [3.2 cm]
	Package Height	0.4 in [10 mm]
	Shipping (Package) Weight	5.2 oz [148.46 g]

What's in the Box	Included in Package	Cable Ties
--------------------------	---------------------	------------

****Product appearance and specifications are subject to change without notice.***

