

USB C Audio & Charge Adapter - USB-C Audio Adapter w/ USB-C Audio Headphone/Headset Port and 60W USB Type-C Power Delivery Pass-through Charger - For USB-C Phone/Tablet/Laptop

Product ID: CDP2CAPDM



This USB C audio adapter with 60W power delivery features a USB Type-C audio port for your headset, audio out or data transfer, while allowing you to charge your laptop, tablet, or smartphone at the same time.


Make calls or listen to music with this USB C audio and charging adapter. The 2 in 1 headphone adapter with charge port allows you to use your USB-C headsets, speakers, or transfer data (USB 2.0 speeds) while simultaneously charging your device through Power Delivery pass through with Type C power adapter connected.

The USB C audio adapter features a cable-less, dongle design with a convenient side-port layout to reduce cable clutter, making it perfect for professionals at their workstation or on-the-go. Constructed of high-quality materials, the portable adapter provides a reliable and affordable audio and charge solution for your USB Type-C devices.

This USB C headset adapter is universally compatible enabling you to use your wired headphones with your USB Type-C or Thunderbolt 3 device, including the MacBook Pro, iPad Pro, Samsung Galaxy and Note.

CDP2CAPDM is backed by a StarTech.com 3-year warranty, and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Listen to music or make phone calls, while charging your USB-C device at the same time
- Virtual conference calls or customer service applications

Features

- **ADD USB-C AUDIO & CHARGING:** USB C audio and charge adapter with a USB-C port for a headset, headphones or for USB 2.0 data transfer (480Mbps) and a second USB-C port for PD pass-through to simultaneously charge your device using a single USB Type-C port
- **MULTIPLE CHARGING MODES:** USB C headphone and charger adapter is bus-powered or use external Type-C power adapter to provide up to 60W Power Delivery 3.0 pass-through to keep your USB-C laptops, tablets and smartphones charged
- **CONVENIENT SIDE PORT LAYOUT:** Compact, horizontal-style adapter w/ cable-less, dongle-like design and discreet side port locations for audio & power connections at opposite ends of the adapter to avoid snags/tangles and to allow for a flexible device setup
- **WIDE COMPATIBILITY:** Works w/ USB Type-C and Thunderbolt 3 laptops, tablets, smartphones & PCs including Lenovo X1 Carbon, MacBook Pro/Air, Surface Pro 7/Book, Chromebook, iPad Pro & Samsung Galaxy/Note
Compatible w/ Windows, macOS, iPadOS & Android
- **PORTABLE DESIGN:** 2-in-1 USB C audio adapter with a compact/leek design can be transported, even when connected to your USB C device between office, home office or for business travel Ideal for conference calls, customer support or at your workstation

Hardware

Warranty	3 Years
Ports	2
Audio	Yes
Chipset ID	BCC-2102

Performance

Maximum Data Transfer Rate	USB 2.0
----------------------------	---------

Connector(s)

Connector A	1 - USB Type-C (24 pin) USB Power Delivery Only
-------------	---

Connector B	1 - USB Type-C (24 pin) USB Power Delivery Only
	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

Software

OS Compatibility	Windows 11, 11 ARM, 10 macOS Sonoma (14.0), macOS Ventura (13.0), Monterey (12.0), Big Sur (11.0), Catalina (10.15), Mjave (10.14), High Sierra (10.13) Android
------------------	---

Power

Power Delivery	60W
----------------	-----

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10-85% RH (no condensation)

Physical Characteristics

Color	Silver
Material	Metal
Product Length	2.0 in [5.0 cm]
Product Width	0.9 in [2.3 cm]
Product Height	0.4 in [0.9 cm]
Weight of Product	0.3 oz [9.0 g]

Packaging Information

Package Quantity	1
Package Length	3.5 in [8.9 cm]
Package Width	3.0 in [7.6 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package)	0.4 oz [10.0 g]

Weight

What's in the Box

Included in Package	1 - USB-C Audio & Charging Adapter
---------------------	------------------------------------

****Product appearance and specifications are subject to change without notice.***