

USB C Multiport Video Adapter - USB-C to 4K 60Hz DisplayPort 1.2 or 1080p VGA Monitor Adapter
- USB Type-C 2-in-1 DP (HBR2 HDR)/VGA Display Converter- Thunderbolt 3 Compatible

Product ID: CDP2DPVGA



This USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a DisplayPort or VGA display. The adapter supports High Dynamic Range (HDR) and provides sharper images with enhanced video.

Avoid the hassle of carrying different adapters, with a 2-in-1 USB-C monitor adapter. Featuring both DisplayPort and VGA outputs, you can conveniently connect your laptop to any DP or VGA-equipped display, using this multiport adapter.

The adapter features a durable aluminum enclosure and can withstand being carried in your travel bag.

The DisplayPort output on this USB-C video adapter lets you harness the audio and video capabilities that are built into your computer's USB-C connection, delivering the astonishing quality of UHD to your 4K 60Hz display. Plus, the VGA output supports HD resolutions up to 1920 x 1080, ensuring you won't have to sacrifice picture quality when connected to a VGA monitor or projector.

With HDR support, you can enjoy lifelike images with increased contrast, brightness and colors and greater luminosity than standard digital imaging.

The USB-C display adapter has a Space Gray housing and built-in USB-C cable designed to match your Space Gray MacBook or MacBook Pro. The adapter is compatible with USB-C DP Alt Mode devices.

CDP2DPVGA is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Note: This adapter only supports a single display - you are not able to output DisplayPort and VGA video simultaneously.

Certifications, Reports and Compatibility

Applications

- Connect to virtually any DisplayPort or VGA display while traveling or in the office
- Output video to a secondary DP or VGA monitor
- Stream, view and edit 4K and HD video on your DisplayPort or VGA display

Features

- **HIGH PERFORMANCE:** USB C (DP Alt Mode) to DisplayPort 1.2 4K 60Hz HBR2 or VGA 1080p display adapter on a single monitor with 2ch audio, compatible with HDCP 2.2/1.4 and Thunderbolt 3 (TB3)
- **FLEXIBLE VIDEO OUTPUT:** 2-in-1 portable USB-C multiport video adapter converter w/ DP 1.2 or VGA, is the perfect video hub for working from a home or office workstation, boardrooms or travel
- **COMPATIBILITY:** USB-C adapter for devices like Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface Pro 7/Laptop 3, MacBook Pro/Air, HP Elite/EliteBook/Spectre/Zbook & Chromebook
- **TESTED & VERIFIED:** USB-C video adapter tested for peak performance @ 4K 60Hz (DP) & 1080p (VGA) on monitors/projectors/displays incl brands like Samsung, Dell, HP, Lenovo, Asus, Acer, LG, Sharp, Sony
- **EASY TO USE:** USB C (DisplayPort over USB-C) display adapter for any TB3/USB Type C laptop/tablet/smartphone & supports driverless plug & play in Windows, macOS, iPadOS, Chrome OS, Linux, Android

Prominence

Warranty	3 Years
Description CDW 75 - 1st Line	StarTech.com USB C Multiport Video Adapter - USB-C to 4K 60Hz DP or VGA

Hardware

AV Input	USB-C
AV Output	DisplayPort - 1.2 VGA
Audio	Yes
Chipset ID	Parade Technologies PS8338

Performance

Maximum Cable Distance To Display	6.6 ft [2 m]
Video Revision	DisplayPort 1.2



Supported Resolutions	DisplayPort; 3840x2160 (4K) / 60Hz VGA: 1920x1080 / 60Hz Lower resolutions and refresh rates may also be supported
Wide Screen Supported	Yes
Audio Specifications	DisplayPort - 2 Channel Audio VGA - No Audio Support

Connector(s)

Connector A	USB-C (24 pin) DisplayPort Alt Mode
Connector B	DisplayPort VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

Note	Your USB-C device must support DP Alt Mode to work with this adapter This adapter only supports a single display - you are not able to output DisplayPort and VGA video simultaneously To achieve HDR, your USB-C port must support DisplayPort 1.4 and your display must support HDMI 2.0b
------	---

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 55C (14F to 131F)
Humidity	5~90% RH (no condensation)

Physical Characteristics

Color	Space Gray
Material	Aluminum
Product Length	2.4 in [62.0 mm]
Product Width	1.7 in [44 mm]
Product Height	0.6 in [15 mm]



Weight of Product	1.8 oz [50 g]
-------------------	---------------

Packaging Information

Package Length	7.0 in [17.8 cm]
----------------	------------------

Package Width	3.1 in [80 mm]
---------------	----------------

Package Height	0.8 in [20 mm]
----------------	----------------

Shipping (Package) Weight	2.5 oz [72 g]
---------------------------	---------------

What's in the Box

Included in Package	USB-C to DisplayPort and VGA Adapter
---------------------	--------------------------------------

****Product appearance and specifications are subject to change without notice.***

