

6ft/1.8m USB C to DisplayPort 1.2 Cable 4K 60Hz - USB-C to DisplayPort Adapter Cable HBR2 - USB Type-C DP Alt Mode to DP Monitor Video Cable - Works w/ Thunderbolt 3 - Black

Product ID: CDP2DPMM6B



This USB-C to DisplayPort cable lets you connect your Thunderbolt 3 or USB Type-C enabled device to a 4K DisplayPort monitor with just one cable, providing you with a convenient, clutter-free solution.

The USB C to DisplayPort adapter cable lets you harness the video capabilities that are built into your USB-C connection, to deliver the astonishing quality of Ultra HD to your 4K display and supporting resolutions up to 3840x 2160.

Plus, the adapter is backward compatible with 1080p displays, which makes it a great accessory for home, office or other work environments.

At 6 ft. (1.8 m) in length, this monitor cable eliminates the need for excess adapters and cabling, ensuring a tidy, professional installation. For installations requiring shorter or longer connections we also offer a 9.8 ft. (3 m) ([%product id="CDP2DPMM3MB" text="CDP2DPMM3MB"%], [%product id="CDP2DPMM3MW" text="CDP2DPMM3MW"%]) and a 3.3 ft. (1 m) ([%product id="CDP2DPMM1MB" text="CDP2DPMM1MB"%], [%product id="CDP2DPMM1MW" text="CDP2DPMM1MW"%]) USB-C to DP cable, enabling you to choose the right cable length for your custom installation needs.

To ensure easy operation and installation, this USB C to DisplayPort cable works with both Windows and Mac computers and allows for plug-and-play installation, removing the need for any additional software or drivers.

CDP2DPMM6B is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Note: Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.

Certifications, Reports and Compatibility



Applications

- Connect USB-C or Thunderbolt 3 devices to DP displays
- Ideal for home office or hot desk environments
- Experience enhanced imaging with support for 4K 60Hz
- Deliver enriched presentations on the go

Features

- **HIGH PERFORMANCE:** Black 6'/1.8m USB-C DP Alt Mode to DisplayPort 1.2 (21.6Gbps) Cable supports 4K 60Hz UHD (3840x2160), HBR2, 5.1ch Audio, HDCP 2.2/1.4 1080p & Thunderbolt 3 Compatible
- **INTEGRATED VIDEO ADAPTER CABLE:** USB C to DisplayPort 1.2 cable (male/male) reduces clutter, minimizes signal loss/failure points & has slim host & display connectors that fit in tight spaces
- **HOST COMPATIBILITY:** Dell XPS, Precision & Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Microsoft Surface & Surface Pro, MacBook Pro, iPad Pro, TB3 MacBook Air, HP EliteBook, Spectre & ZBook
- **DISPLAY COMPATIBILITY:** USB-C to DP cable is tested & verified w/ full range of DP monitors incl brands Dell, Samsung, Asus, Acer & LG
- **EASY TO USE:** DisplayPort over USB-C converter cable w/ driverless setup works w/ any USB Type-C/Thunderbolt 3 (DP Alt Mode) device; compatible w/ macOS, iPadOS, Windows 10, Chrome OS, Android & Linux

| | | |
|---------------------|---------------------------------|-------------------------------------|
| Hardware | Warranty | 3 Years |
| | AV Input | USB-C |
| | Ports | 1 |
| | AV Output | DisplayPort - 1.2 |
| | Chipset ID | STMicroelectronics - STM32F072CBU6 |
| Performance | Video Revision | DisplayPort 1.2 |
| | Maximum Digital Resolutions | 3840 x 2160 @ 60 Hz |
| | | 1024x768 |
| | Supported Resolutions | 1280x720 (High-definition 720p) |
| | | 1920x1080 (High-definition 1080p) |
| | Wide Screen Supported | 1920x1200 |
| | | 2560x1440 |
| | Audio Specifications | 2560x1600 |
| | | 3840x2160 (Ultra HD 4K) |
| | | Yes |
| | DisplayPort - 5.1 Channel Audio | |
| Connector(s) | Connector A | USB-C (24 pin) DisplayPort Alt Mode |

Connector B DisplayPort (20 pin)

| | | |
|-------------------------------------|-------------------------------|---|
| Special Notes / Requirements | System and Cable Requirements | Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter. |
| Environmental | Operating Temperature | 0C to 40C (32F to 104F) |
| | Storage Temperature | -40C to 80C (-40F to 158F) |
| | Humidity | 20%-70%RH |
| Physical Characteristics | Color | Black |
| | Cable Length | 5.9 ft [1.8 m] |
| | Product Length | 5.9 ft [1.8 m] |
| | Product Width | 0.8 in [20 mm] |
| | Product Height | 0.4 in [10 mm] |
| | Weight of Product | 1.7 oz [49 g] |
| Packaging Information | Package Length | 8.7 in [2.2 cm] |
| | Package Width | 7.9 in [2 cm] |
| | Package Height | 0.7 in [19 mm] |
| | Shipping (Package) Weight | 2.0 oz [58 g] |
| What's in the Box | Included in Package | USB-C to DisplayPort Cable |

****Product appearance and specifications are subject to change without notice.***

