

USB-C to HDMI Adapter with 4K 30Hz - Black

Product ID: CDP2HD



This USB-C to HDMI adapter lets you to output 4K video and audio from the USB Type-C port on your laptop to an HDMI display or projector. The adapter works with USB 3.1 or Thunderbolt 3 Type-C devices that pass a DP video signal, such as your MacBook Pro, Chromebook or 2018 iPad Pro.

This video adapter is also available in white ([%product id="CDP2HDW" text="CDP2HDW"%]).

This adapter lets you harness the video capabilities from your computer's USB-C connection, to deliver the astonishing quality of UHD to a 4K 30Hz display.

You can achieve an output resolution of up to 3840 x 2160p at 30Hz, perfect for performing high-resolution tasks. Plus, the USB-C display adapter is backward compatible with 1080p monitors and displays, making it a great accessory for any workspace application.

This HDMI converter lets you use the versatile USB Type-C port on your portable device. USB-C is a reversible connector, so you can plug it to your device in any direction. Plus, it's Thunderbolt 3 compatible, providing a hassle-free connection to your Windows or Mac based Thunderbolt 3 computer.

This compact, lightweight USB-C video adapter is easy to carry in your laptop bag. It's ideal for BYOD (Bring Your Own Device) applications at the office and is compatible with any device that supports USB-C DP Alt Mode.

CDP2HD is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your laptop to a provided HDMI display at work
- Deliver presentations from USB-C laptops to HDMI displays
- Connect an HDMI monitor to your USB-C laptop as a secondary display

Features

- Obtain high performance picture quality from your USB-C device with support for UHD video resolutions up to 4K 30Hz
- Connect easily with the reversible USB-C connector
- Compatible with Thunderbolt 3 and USB Type-C with DisplayPort Alt Mode
- Maximum portability with a compact, lightweight design

Hardware	Warranty	3 Years
	AV Input	USB-C
	Ports	1
	AV Output	HDMI - 1.4
	Audio	Yes
	Chipset ID	Parade - PS171
		STMicroelectronics - STM32F072CBU6

Performance	Maximum Cable Distance To Display	49.9 ft [15.2 m]
	Video Revision	HDMI 1.4
	Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @30hz
	Supported Resolutions	1024x768
	Wide Screen Supported	1280x720 (High-definition 720p)
	Audio Specifications	1920x1080 (High-definition 1080p)
		1920x1200
		2560x1440
		2560x1600
		3840 x 2160 (Ultra HD 4K) @30hz

Connector(s)	Connector A	USB-C (24 pin) DisplayPort Alt Mode
	Connector B	HDMI (19 pin)

Special Notes / System and Cable Your USB-C port must support DisplayPort over USB-C (DP Alt mode)

Requirements Requirements in order to work with this adapter.

Environmental	Operating Temperature	0 C to 45 C
	Storage Temperature	-20 C to 60 C
	Humidity	25-85%

Physical Characteristics	Color	Black
	Material	Plastic
	Cable Length	2.6 in [67 mm]
	Product Length	5.8 in [1.5 cm]
	Product Width	0.9 in [23 mm]
	Product Height	0.4 in [9 mm]
	Weight of Product	0.8 oz [22 g]

Packaging Information	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2 cm]
	Package Height	0.4 in [10 mm]
	Shipping (Package) Weight	1.1 oz [30 g]

What's in the Box	Included in Package	USB-C to HDMI adapter
--------------------------	---------------------	-----------------------

**Product appearance and specifications are subject to change without notice.*

