

Vertical Cable Organizer with Finger Ducts - 0U - 6 ft.

Product ID: CMVER40UF



This 6-foot vertical cable manager (2x3-foot panels) gives you a simple and space-efficient way to organize the cables in your server rack. You can attach the two-panel cable manager vertically into your rack, to neatly guide cables between equipment that's mounted at different heights.

The 0U cable manager offers versatile installation options and is compatible with most racks that are 40U or larger. The panels feature a 0U design that doesn't take up any mounting space, and with simple tool-less installation, they're easy to attach or reposition as necessary.

The vertical cable manager uses a finger-duct method of cable management, which includes a cover panel that neatly conceals the cables that are running through it.

Having well organized and routed cables not only improves the appearance and accessibility of your rack, it also makes it easier for you to install, access and maintain rack components.

This versatile cable management system consists of two 3-foot panels, so you can configure each panel as needed to accommodate all of your equipment. You can install the individual panels end to end (top to bottom) so that they span the height of your rack, or on either side or the front and back of your rack to manage cables in multiple locations.

The two-piece cable manager runs vertically along the side of your rack, to neatly guide cables between equipment that's mounted at different heights. This provides a tidy and well-organized way to run cables from devices mounted toward the bottom of your rack to other devices mounted near the top, without leaving a mess of cables hanging in between.

For maximum compatibility with virtually any server rack, you can install the cable-management panels using mounting holes that are commonly found on most rack equipment. The tool-less mounting method attaches the cable management panel to the keyhole-shaped mounting holes that are built into your rack.

The horizontal mounting rail method attaches the cable management panel to the horizontal mounting rails that run along the side of your rack.

For racks that don't support these installation methods, you can also mount the cable management panels through other means, such as using the non-standardized holes found on your rack walls and enclosures, or the rack units on equipment mounting rails.

Routing your cables through a panel reduces the tension that's often put on cables. This prevents cable damage or connection loss, and reduces strain on equipment ports, preventing damage to your expensive rack-mounted devices.

Properly routing cables also improves airflow, which passively cools devices stored in your rack, helping to keep your equipment running at optimal temperatures to reduce the probability of damage caused by your rack overheating.

The CMVER40U is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Guide cables from a server that's mounted toward the bottom of your rack to patch panels that are mounted near the top
- Run cables in your rack to the side, in order to improve airflow
- Keep rack-mounted equipment accessible

Features

- Improve the appearance of your rack using a vertical cable manager with finger ducts
- Promote passive cooling in your rack by organizing cables to improve airflow
- Make your rack more accessible by organizing your cables for hassle-free maintenance and scalability
- 6-feet (40U) in height
- Helps eliminate cable stress, to protect your equipment from damages caused by sudden cable tension

Hardware	Warranty	2 Years
	Frame Type	Steel and Plastic
	U Height	40U
	Orientation	Vertical
	Mounting Options	Front Mount (Front and Rear)
Physical Characteristics	Color	Black
	Material	Steel and Plastic
	Product Length	5.6 ft [1.7 m]
	Product Width	3.9 in [100.000 mm]
	Product Height	2.9 in [73.000 mm]

	Weight of Product	3.8 lb [1.7 kg]
Packaging Information	Package Length	13.8 in [3.5 cm]
	Package Width	9.2 in [2.3 cm]
	Package Height	6.7 in [1.7 cm]
	Shipping (Package) Weight	5.2 lb [2.4 kg]
What's in the Box	Included in Package	vertical cable organizers
	Included in Package	M5 cage nuts
	Included in Package	M5 cage screws
	Included in Package	M4 nuts
	Included in Package	instruction manual

**Product appearance and specifications are subject to change without notice.*

