

4 Port Component Video Switch with Digital Audio and Remote

Product ID: CPNT410IR



StarTech.com's 4-Port Component Video Switch lets you switch between up to four A/V devices as well as the corresponding audio signals, eliminating the need to swap out cables to make use of multiple audio/video devices.

A versatile solution for home theatre applications requiring digital or analog audio connections with the use of standard and HD component devices, the 4-port Component Video switch supports display resolutions ranging from 480i to 1080i, providing the signal quality necessary to bring out the best results from your input devices.

A convenient, time-saving A/V solution, the Component Video switch can be installed in minutes and offers a remote learning feature that allows you to use existing device remotes to toggle between inputs, in addition to the IR remote control that is included with the Component switcher.

This attractive, compact unit can be installed in minutes, and is backed by a 2-year warranty as well as free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect and switch between four component video devices to one TV / HDTV display
- Excellent for home theatre applications requiring digital or analog audio connections with the use of standard and HD component devices

Features

- Connect up to four devices to your TV using a single set of inputs
- With the Remote Learning feature, program the video switch to work with your existing universal remote
- Maintains clear audio and video signals for excellent performance

Hardware

Warranty	2 Years
AV Input	Component
	Digital Coaxial
	Audio RCA
Ports	4
AV Output	Component
	Digital Coaxial
	Audio RCA
Audio	Yes

Performance

Maximum Analog Resolutions	Supports standard and high definition video resolutions. 480i to 1080i.
----------------------------	-------------------------------------------------------------------------

Connector(s)

Connector A	4 - Component Video (3 x RCA)
	4 - Digital Coax Audio (RCA)
	4 - Stereo Audio (2 x RCA)
Connector B	1 - Component Video (3 x RCA)
	1 - Digital Coax Audio (RCA)
	1 - Stereo Audio (2 x RCA)

Special Notes / Requirements

System and Cable Requirements	Requires a standard or high definition display with a component video (YPbPr) video input
-------------------------------	-------------------------------------------------------------------------------------------

Power

Power Source	AC Adapter Included
Input Voltage	120 AC
Input Current	0.1A
Output Voltage	9V DC
Output Current	0.2A
Center Tip Polarity	Positive
Power Consumption (In Watts)	1.8

Physical Characteristics

Color	Silver
Material	Plastic
Product Length	9.2 in [23.3 cm]
Product Width	6.4 in [16.2 cm]
Product Height	1.7 in [4.4 cm]
Weight of Product	21.9 oz [620 g]

Packaging Information

Package Quantity	1
Package Length	6.8 in [17.2 cm]
Package Width	2.5 in [64 mm]
Package Height	14.2 in [36 cm]
Shipping (Package) Weight	1.8 lb [0.8 kg]

What's in the Box

Included in Package	1 - Component/Audio Switcher
	1 - Remote Control

1 - 9V DC Power Adapter

1 - Instruction manual

**Warranty
Information**

Warranty

2 Years

**Product appearance and specifications are subject to change without notice.*