

2U Double-Sided Horizontal / Vertical Cable Management Panel with Finger Duct & D-Ring Hooks

Product ID: CMPNL2UC



The CMPNL2UC 2U Cable Management Panel mounts to a standard 19" 2 or 4-post rack to help you organize both horizontal and vertical cabling, using the combination of a finger duct and D-Ring hooks. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed of high-quality steel, the cable organizer is designed as a double-sided solution offering cable management on both the front and back of the panel. The front is equipped with 4 vertical and 4 horizontal D-Ring hooks, while the back has 2 additional hooks as well as a cable duct with a series of fingers that help you route your cables where you need them, and reduce cable strain in the process.

As an added benefit, the panel also promotes proper airflow through the rack by closing off open spaces between equipment. For easy installation, this horizontal cable organizer comes complete with 2 sets of rack screws (10/32 and 12/24).

Note: The hooks on this cable management system extend past 19 inches. As a result certain racks with close spaced or inset rack mount holes may not be compatible with this product.

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Use with server racks and cabinets, structured wiring closets and network distribution cabling to keep cables neat and tidy

Features

- D-Ring hooks on the front (x4) and the back (x2) of the panel
- Finger duct on the back for routing cables
- 2U rack design
- Sturdy steel construction
- Mounts to standard 19" 2 or 4-post server racks
- Includes rack screws
- TAA compliant for GSA Schedule purchases

Hardware

Warranty	2 Years
U Height	2U
Industry Standards	EIA RS310-D
Orientation	Horizontal
Mounting Options	Front Mount (Front Only)

Physical Characteristics

Color	Black
Material	Steel
Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	3.3 lb [1.5 kg]

Packaging Information

Package Length	22.2 in [56.3 cm]
Package Width	5.0 in [12.6 cm]
Package Height	4.3 in [10.8 cm]
Shipping (Package)	4.3 lb [1.9 kg]



Weight

**What's in the
Box**

Included in Package	2U Combo Cable Manager
	Cable Clamps
	5/8" #10-32 UNF Screws
	5/8" #12-24 UNC Screws
	#10-32 UNF Cage Nuts
	#12-24 UNC Cage Nuts

****Product appearance and specifications are subject to change without notice.***

