

Under-Desk CPU Mount - Adjustable

Product ID: CPUMNTUD



Maximize your workspace. This under-desk CPU mount frees up floor and desk space, and gives you easy access to your computer tower.

The under-desk CPU holder provides an easy way to mount your computer under any desk or flat surface. It helps keep your work space neat and organized, by mounting your computer case off the desktop or floor, away from dust and dirt. The under-desk PC mount is ideal for mounting your CPU under a standing or sit-stand desk, moving the CPU up and down along with the desktop as needed.

The heavy-duty CPU holder has an adjustable frame that supports a variety of PC cases, ranging in width from 4.84" to 9.96" (123 mm to 253 mm) and height from 14" to 21.9" (357 mm to 557 mm).

Offering a full 360-degree swivel, the under-desk PC mount provides easy access to your computer case, front and back, ensuring ports and cables are easy to reach. The under-desk CPU holder has a 10.09" (485 mm) long track with an easy-glide sliding mechanism that allows the CPU to move sideways for enhanced accessibility.

The heavy-duty computer tower mount securely holds your PC case, with a weight capacity of up to 66 lb. (30 kg).
CPUMNTUD is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount your computer under your desk or table to save space
- Ideal for mounting your CPU under a standing desk or sit-stand desk

Features

- Save space by mounting your PC case under your desk, off the floor
- Fits most CPU towers, with an adjustable frame (4.84" to 9.96" width and 14" to 21.9" height)
- Heavy-duty CPU mount securely holds up to 66 lb. (30 kg)
- Full 360-degree swivel for easy access to ports and cables
- Easy installation with all hardware needed for setup included

| | | |
|---------------------------------|-------------------------------|--|
| Hardware | Warranty | 5 Years |
| | Mounting Options | Under Desk |
| Performance | General Specifications | Adjustable Frame: 4.84" to 9.96" (123 mm to 253 mm) width and 14" to 21.9" (357 mm to 557 mm) height |
| | Weight Capacity (Per Display) | 66.3 lb [30 kg] |
| | Swivel / Pivot | 360 |
| Physical Characteristics | Color | Black |
| | Material | Steel and Plastic |
| | Product Length | 8.4 in [2.1 cm] |
| | Product Width | 10.0 in [2.5 cm] |
| | Product Height | 26.2 in [6.6 cm] |
| | Weight of Product | 11.0 lb [5.0 kg] |
| Packaging Information | Package Length | 10.2 in [2.6 cm] |
| | Package Width | 9.6 in [2.4 cm] |
| | Package Height | 21.5 in [5.5 cm] |
| | Shipping (Package) Weight | 12.0 lb [5.4 kg] |
| What's in the Box | Included in Package | CPU Holder |
| | Included in Package | Mounting Plate |
| | Included in Package | Stoppers |
| | Included in Package | Mounting Screws |
| | Included in Package | Foam Sheet |
| | Included in Package | User Manual |
| | Included in Package | Stopper Screws |

**Product appearance and specifications are subject to change without notice.*

