

## DisplayPort 1.2 Cable with Latches - Certified, 10 ft

Product ID: DISPLPORT10L



This DisplayPort cable provides a secure connection between your DisplayPort equipped devices and is capable of providing higher performance than either HDMI or dual-link DVI.

The DP cable supports high resolutions of up to 4K x 2K (4096 x 2160, 60Hz) with a maximum HBR2 bandwidth of 21.6Gbps, as well as optional audio support. The cable also supports Multi-Stream Transport (MST) for daisy chaining multiple monitors.

The 10-foot cable is DisplayPort (VESA) certified to support DP 1.2 specifications and ensure a high-quality, reliable connection for all of your DisplayPort devices.

The DISPLPORT10L is backed by a StarTech.com lifetime warranty for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

## Certifications, Reports and Compatibility



## Applications

- Connecting a DisplayPort display to a PC or other DisplayPort source

## Features

- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- High-resolution support up to 4K x 2K
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6Gbps
- Backward compatible with DisplayPort 1.1

- Designed and manufactured to DisplayPort 1.2 standards
- Molded latching connectors with strain relief
- DisplayPort (VESA) certified

<b>Hardware</b>	Warranty	Lifetime
	Number of Conductors	19
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CMG Rated (General Purpose)
<b>Performance</b>	General Specifications	Insertion Rating: 5000
<b>Connector(s)</b>	Connector A	DisplayPort (20 pin)
	Connector B	DisplayPort (20 pin)
<b>Environmental</b>	Operating Temperature	0 to 50 C
	Storage Temperature	-20 to 70 C
	Humidity	0 to 95%
<b>Physical Characteristics</b>	Color	Black
	Connector Style	Latching
	Wire Gauge	28 AWG
	Cable Length	10.0 ft [3.0 m]
	Cable OD	0.3 in [7.3 mm]
	Product Length	10.0 ft [3.0 m]
	Product Width	0.8 in [20.500 mm]
	Product Height	0.4 in [10.800 mm]
	Weight of Product	7.4 oz [210.000 g]
<b>Packaging Information</b>	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	1.3 in [34.000 mm]
	Shipping (Package) Weight	7.6 oz [215.000 g]

<b>What's in the Box</b>	Included in Package	10 ft DisplayPort Cable 1.2 with Latches - M/M
--------------------------	---------------------	--

---

*\*Product appearance and specifications are subject to change without notice.*

