

USB-C USB-A Dock - Hybrid Universal USB 3.0 Docking Station for USB-C or USB-A Laptop - Dual Monitor 4K 60Hz HDMI/DisplayPort - 6x USB-A, GbE - USB 3.1/3.2 Gen 1 - Windows/Mac

Produkt-ID: DK30A2DHU



Transition from the legacy USB-A (USB 3.1/3.0) to newer USB-C laptops with this universal laptop docking station for USB-C and USB-A laptops. The USB 3.1 Gen 1 (5 Gbps) Type-C dock features dual HDMI and/or DisplayPort monitors, six USB Type-A downstream peripheral ports, and headset audio.

This is a dual 4K60Hz video docking station with support for both Ultra HD DisplayPort and/or HDMI monitors that lets you configure your video connections to best suit your needs.

Dual 4K DisplayPort | Up to 4096 x 2160p @ 60Hz

Dual 4K HDMI | Up to 4096 x 2160p @ 60Hz

Single 4K DisplayPort + Single 4K HDMI | Up to 4096 x 2160p @ 60Hz

Single 5K DisplayPort* | Up to 5120 × 2880

*Requires monitor support for 5K using two DP ports

This docking station is fully certified to meet top industry standards for DisplayLink (video connections) certification to guarantee the highest quality, performance, and compatibility.

For fast setup right out of the box, the two included host cables (USB-C and USB-A) connect to any laptop. The included dock stand lets you position the dock vertically to save space or lay flat on the desk.

Connect your devices with six downstream USB Type-A (USB 3.0 5 Gbps) ports, two positioned on the front, and four on the back. The dock provides a GbE port and a 3.5 mm 4-position headset audio jack.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite includes:

Advanced Windows Layout Utility: To setup and save custom windows layouts.

Mac Address Pass-Through Utility: To improve network security.

USB Event Monitoring Utility: To track and log connected USB devices

Wi-Fi Auto Switch Utility: Enabling users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:
www.StarTech.com/Connectivity-Tools

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

DK30A2DHU is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- LATEST MODEL: This USB-C USB-A dock offers the same functionality as DK30A2DH, with added flexibility of horizontal or vertical orientation using the included stand to save space at your workstation

- **HYBRID DOCK:** Universal USB 3.0 docking station works w/ USB-C & USB-A laptops/computers and features a 6-Port USB Type-A hub, Gigabit Ethernet & headset audio jack; NOTE: This dock does not provide USB-C Power Delivery to charge your laptop
- **FLEXIBLE DUAL MONITOR VIDEO:** This 4K 60Hz USB-C or USB-A docking station can connect up to 2 monitors: Dual DisplayPort or Dual HDMI or DP + HDMI displays; supports dual extended displays on MacBooks with both the Intel processor or Apple M1/M2 chip
- **6 DOWNSTREAM USB-A PORTS:** Hybrid USB C dock has a 6-port USB 3.1/3.2 Gen 1 (5Gbps) hub w/ extra USB-A ports to support devices such as keyboard, mouse, flash drive, external hard drive & printer
- **COMPATIBILITY:** USB-C port replicator is DisplayLink Certified for max. performance & compatible w/ Dell, HP, Lenovo & MacBook PCs; Windows, ChromeOS and macOS platforms, where mixed laptop Brands used; Includes USB-C and USB-A host cables
- **CONNECTIVITY TOOLS:** Die mit diesem Gerät gelieferte Anwendung verbessert Leistung und Sicherheit und bietet MAC Address Changer, USB Event Monitoring, Fensteranordnung & Wi-Fi Auto Switch Dienstprogramme

Hardware

Garantiebestimmungen	3 Years
4K-Unterstützung	Ja
Schnellladeanschlüsse	Nein
Unterstützte Displays	2
Ports	8
Audio	Ja
Schnittstelle	USB 3.2 Gen 1
Bustyp	USB-C
USB-Passthrough	Ja
Chipset-ID	DisplayLink - DL-6950
	VIA/VLI - VL813
	Realtek - RTS5411T

Leistung

Wake On Lan	Ja
-------------	----

Max. Digitalauflösungen	4K 60 Hz
Kompatible Netzwerke	10/100/1000 Mbps
Allgemeine Spezifikationen	Wake-on-LAN (WoL): Yes
MTBF	26 280 hrs

Steckverbinder

Steckverbindertyp(en)	6 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps) 1 - RJ-45 2 - HDMI 2 - DisplayPort 1 - 3,5-mm-Audio
Hostanschlüsse	1 - USB 3.2 USB Type-B (9 pin, Gen 1, 5 Gbps)

Software

Betriebssystemkompatibilität	Windows® XP (32-Bit), Vista, 7, 8, 8.1, 10, 11 macOS 10.6 – 10.12, 10.14 – 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1 Ubuntu 18.04, 20.04, 22.04, 24.04 Chrome OS™ v55+
------------------------------	---

Spezielle Hinweise/Anforderungen

Hinweis	DisplayLink docking stations and video adapters support more than one external display on Apple's M1-based Mac. Requires driver installation. Please contact StarTech.com support for a recommendation based on your specific setup.
---------	--

Strom

Stromversorgung	Mit Netzadapter
Eingangsspannung	110V-240V AC
Eingangsstrom	1.0A

Ausgangsspannung	20V DC
Ausgangsstrom	2A
Steckertyp	N
Stromverbrauch	40W

Umgebungsbedingungen

Betriebstemperatur	0 to 50°C
Lagertemperatur	-20 to 70°C
Feuchtigkeit	0 % bis 95 % (nicht kondensierend) bei 25°C

Physische Eigenschaften

Farbe	Black & Gray
Gehäusety	Aluminium und Kunststoff
Kabellänge	3.3 ft [1 m]
Produktlänge	2.9 in [7.3 cm]
Produktbreite	5.3 in [13.5 cm]
Produkthöhe	7.4 in [18.7 cm]
Produktgewicht	12.0 oz [340.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	8.3 in [21.2 cm]
Paketbreite	4.5 in [11.4 cm]
Pakethöhe	5.7 in [14.4 cm]
Versandgewicht (Verpackung)	1.7 lb [0.8 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Docking Station
--------------------	---------------------

1 - USB-C-zu-USB-B-Kabel

1 - USB-A-zu-USB-B-Kabel

1 - Universal Power Adapter (NA/JP, ANZ)

1 - Dock Stand

1 - Quick-Start Guide

Garantieinformatio
nen

Warranty

3 Jahre

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.