USB-C Dock - Dual Monitor 1080p HDMI Laptop Docking Station - 65W Power Delivery - 1x USB-C, 3x USB-A, Ethernet - Dual Video Display USB 3.1 Gen 1 Type-C Dock - Mac & Windows

Product ID: DK30CHHPDUK



This USB-C docking station is ideal for use in large organizations to meet widespread office productivity requirements and compatibility with all USB-C and Thunderbolt 3 laptops. The USB-C dock features support for Dual HDMI monitors, 65W Power Delivery 3.0, fast-charge, and both USB-C and USB-A peripheral ports.

The USB-C docking station adds dual HDMI monitors support to your workstation, with full high definitions resolutions of 1920x1080 or 1920x1200 at 60Hz. With more screen space, you can access multiple applications and reference material on one display while composing on the other.

The USB-A and USB-C charge ports can charge your smartphone, tablet or other USB peripherals whether you're working or away from your desk, and even if you disconnect your laptop.

Using a single cable, the dock powers and charges your laptop as you work with 65W PD for faster charging, using the 90W power adapter.

With a smaller size and extended length 3.3' (1 meter) host cable, this USB-C dock fits easily into a workspace environment. Even where desk space is limited, this dock can be mounted to the wall, monitor or underneath the desk with StarTech.com mounting brackets (SSPMSUDWM & SSPMSVESA). These mounting brackets are specifically designed for our docks and hubs to give you the customized setup you need.

Connect your devices with four USB 3.1 ports: 1x USB -C and 3x USB-A. Fast-charge your USB-C or USB-A smartphone. The dock provides a GbE port (Wake-on-LAN) and a 3.5 mm 4-position headset audio jack. It also includes a security lock slot (K-slot) to protect against theft.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite includes:

Advanced Windows Layout Utility: To setup and save custom windows layouts.

Mac Address Pass-Through Utility: To improve network security.

USB Event Monitoring Utility: To track and log connected USB devices

Wi-Fi Auto Switch Utility: Enabling users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit: www.StarTech.com/Connectivity-Tools

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

Certifications, Reports and Compatibility



Applications

Features

• FULL FEATURE USB-C DOCKING STATION: Offers dual screen 1080p HDMI video, 3x USB-A, 1x USB-C, 65W Power Delivery, Gigabit Ethernet and 3.5mm audio providing an efficient USB 3.1 5Gbps docking solution

• COMPATIBILITY: Supports Windows, macOS, ChromeOS, Linux and hardware platforms including Intel, AMD and the Apple M-Series, enabling two external displays even on laptops that natively only support one; Driver installation required on Windows and macOS

• EASY DEPLOYMENT: This USB-C dock supports all major operating systems (Windows, macOS, ChromeOS, Ubuntu) and includes DisplayLink update utilities for hassle-free IT management

• EASY WORKSPACE INTEGRATION: This universal USB 3.0 Type-C dock is designed to fit into any work environment including shared workspaces or hoteling; It features mounting holes, K-Slot & 1m USB-C cable

• POWER & CHARGE YOUR LAPTOP: This USB Type-C port replicator powers and charges while you work with 65W PD for ultrathin laptops like Thinkpad T Series, X1 Carbon, Surface Pro7, & USB-C Chromebooks

General

UPC	065030883481
Package Quantity	1
Warranty	3 Years

Special Notes / Requirements

Special Notes	Linux Support Note(s): Ubuntu 18.04, 20.04 DisplayLink docking stations and video adapters support more than one external display on Apple's M1-based Mac. Requires driver installation. Please contact StarTech.com support for a recommendation based on your specific setup.

Power

Power Source	AC Adapter Included
Power Delivery	65W
Input Voltage	110V-240V AC
Input Current	1.5A
Output Voltage	20V DC
Output Current	4.5 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption	90

Physical & Environmental

Color	Black & Space Gray
Cable Length	3.3 ft [1 m]
Product Length	5.9 in [15.0 cm]
Product Width	3.1 in [80.0 mm]
Product Height	1.2 in [30.0 mm]
Weight of Product	10.6 oz [300.0 g]
Operating Temperature	0 to 50C

	Storage Temperature	-20 to 70C
	Humidity	0% to 95% (non-condensing) at 25C
Performance		
	Maximum Data Transfer Rate	5 Gbps (USB 3.0)</BR>1 Gbps (Ethernet)
	Type and Rate	USB 3.0 (5Gbps)
	UASP Support	Yes
	Compatible Networks	10/100/1000 Mbps
	Full Duplex Support	No
	Wake-On-LAN (WOL)	Yes
	Maximum Digital Resolutions	Dual HDMI Displays: 1080p (1920x1080, 1920x1200 @ 60Hz)
Hardware		
	USB-C Device Port(s)	USB Power Delivery
	USB-C Host Connection	Yes
	4K Support	No
	Displays Supported	2
	Number of Battery Charge 1.2 Ports	1
	Number of Ports	4
	Audio	Yes
	Interface	USB 3.2 Gen 1
	Compatible Lock Slot	Kensington K-Slot
	Number of Displays	2
	Chipset ID	DisplayLink DL3900, Realtek RTS5423, Realtek RTS5411 or RTS5411E
Packaging & In-the-Box		
	Included in Package	1 - Docking Station

		1 - USB-C Host Cable (1 m)
		1 - Universal Power Adapter (UK)
		1 - Quick-Start Guide
	Package Width	9.2 in [23.4 cm]
	Package Depth	5.7 in [14.5 cm]
	Package Height	3.2 in [82 mm]
	Shipping (Package) Weight	2.2 lb [1.0 kg]

Connector(s)

	Connector 1 (Quantity)	1
	Connector 1	USB-C (5Gbps, 4.5W)
	Connector 2 (Quantity)	1
	Connector 2	USB-A (7.5W Power Only)
	Connector 3 (Quantity)	2
	Connector 3	USB-A (5Gbps, 4.5W)
	Connector 4 (Quantity)	2
	Connector 4	HDMI
	Connector 5 (Quantity)	1
	Connector 5	RJ-45
	Connector 6 (Quantity)	1
	Connector 6	3.5mm (4 Conductors, TRRS)
	Connector 7 (Quantity)	1
	Connector 7	USB-C (7.5W Power Only)

Product appearance and specifications are subject to change without notice.