

USB C Mini Dock for Chromebooks, iPad Pro, Android Tablets/Smartphones, USB-C Chromebook Docking Station w/ 4K 30Hz HDMI, 27W Power Delivery Charging, 3-Port USB Hub, Gigabit Ethernet - TAA

Produkt-ID: DK30CHPH



This ultra compact USB-C docking station with 4K 30Hz HDMI, USB-A ports, USB-C Power Delivery, plus gigabit Ethernet connects to your tablet or smartphone to give you a desktop experience from your mobile smart devices, all through a single USB-C connection.

The versatile USB-C adapter lets you create a single-monitor workstation virtually anywhere, providing 4K Ultra HD (3840 x 2160p) HDMI output with 30 Hz refresh rates, one USB 3.2 Gen 1 (5Gbps) port, two USB 2.0 Type-A ports, and a Gigabit Ethernet port.

As one of the smallest on the market, this docking station is ideal for mobile use. Ultra compact, cube style design makes this docking station the ideal accessory to turn tablets, smartphones and thin ultrabooks and notebooks into workstations whether working from home, in shared or cooperative office spaces or for business travel.

This mini USB-C dock for tablets and smartphones, comes with a 45 watt power adapter and supports USB Power Delivery up to 27W, while reserving 18W for the dock itself. Use the included power adapter for downstream PD charging (capped at 45W max.). The adapter also features a USB-C host cable at 1m (3.3 ft), for added flexibility in connecting to your mobile smart device.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite includes:

Advanced Windows Layout Utility: To setup and save custom windows layouts.

Mac Address Pass-Through Utility: To improve network security.

USB Event Monitoring Utility: To track and log connected USB devices

Wi-Fi Auto Switch Utility: Enabling users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:
www.StarTech.com/Connectivity-Tools

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

DK30CHPH is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **iPAD PRO DOCK:** USB-C Minidock, um Ihr iPad Pro oder andere USB-C Tablets in eine funktionsfähige Workstation zu umwandeln, mit 1 m langen USB-C Kabel für eine verlängerte Reichweite, um die Belastung der Ports zu reduzieren und mehr Flexibilität zu bieten
- **POWER DELIVERY:** Mit 27W PD zum schnellen Laden eines iPad Pro oder anderer USB-C Tablets und Smartphones bei gleichzeitiger Nutzung des mobilen Geräts als Workstation; Inklusive eines 45W Stromadapters, um das Minidock mit voller Leistung zu betreiben
- **PORTABILITÄT:** Ultrakompakt mit 6,5 cm x 6 cm x 3,6 cm und 138 g. im Würfelformat macht diese Dockingstation zum idealen Zubehör, um USB-C Tablets/Handys in Arbeitsstationen für die Arbeit von zu Hause, Hot Desks oder Geschäftsreisen zu verwandeln.
- **UMFASSENDE KOMPATIBILITÄT:** Ideal für USB-C Laptops, Tablets und Handys wie Chromebooks, Lenovo Yoga, Pixelbook, HP Elite, iPad Pro, iPhone 15[Plus/Pro/Max] & höher, Samsung Galaxy S8 &

höher; Arbeitet mit Chrome OS, iPadOS, iOS, Windows 10 & Android 9.0

- UNSER VORTEIL: Enthaltene Connectivity Tools für IT-Profis und IT-Helpdesk Support-Teams mit Network MAC Address Pass-Through für Netzwerksicherheit, WiFi Auto Switching für verbesserte Netzwerkleistung, USB Event Monitoring und Windows Layout

Hardware

Garantiebestimmungen	3 Years
4K-Unterstützung	Ja
Schnellladeanschlüsse	Nein
Unterstützte Displays	1
Audio	Nein
Bustyp	USB 3.2 Gen 1 (5 Gbps)
Chipset-ID	Realtek - RTS5411
	Realtek - RTS5434
	Realtek - RTS8153

Leistung

Total USB Power Output	27W
Max. Datenübertragungsrate	5 Gbit/s
Max. Digitalauflösungen	4K 30 Hz
MTBF	10,000 hrs

Steckverbinder

Externe Ports	1 - Barrel-Stromanschluss (Größe M, AD: 5,50, ID: 2.10)
	2 - USB 2.0 Typ-A (4 pin, 480Mbit/s)
	1 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps)
	1 - HDMI

1 - RJ-45

Hostanschlüsse

1 - USB 3.2 Typ-C (24-pin, Gen 1, 5Gbit/s)

Software

Betriebssystemkompatibilität

Windows 10, 11

macOS Tahoe (26.1)

macOS Sonoma (14.0)

macOS Ventura (13.0)

macOS Monterey (12.0)

macOS Big Sur (11.0)

macOS Catalina (10.15)

macOS Mojave (10.14)

macOS High Sierra (10.13)

Ubuntu 18.04, 20.04

iPadOS

Android 9.0

Strom

Stromversorgung Mit Netzadapter

Power Delivery 45W

Eingangsspannung 100 - 240 AC

Ausgangsspannung 20V DC

Ausgangsstrom 3.25A

Steckertyp M

Umgebungsbedingungen

Betriebstemperatur 0°C ~ 40°C

Lagertemperatur -20°C ~ 70°C

Feuchtigkeit 60% ~ 80%

Physische
Eigenschaften

Farbe	Schwarz & spacegrau
Gehäusotyp	Aluminium und Kunststoff
Kabellänge	39.4 in [100 cm]
Produktlänge	2.6 in [6.5 cm]
Produktbreite	2.4 in [6.0 cm]
Produkthöhe	1.4 in [3.6 cm]
Produktgewicht	4.9 oz [138.0 g]

Verpackungsinform
ationen

Paketmenge	1
Paketlänge	6.7 in [17.0 cm]
Paketbreite	7.5 in [19.1 cm]
Pakethöhe	3.9 in [9.9 cm]
Versandgewicht (Verpackung)	1.5 lb [0.7 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Dockingstation
	1 - 1 m USB-C-Kabel
	1 - Netzadapter
	1 - Kurzanleitung

Garantieinformatio
nen

Warranty	3 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.