

USB C Multiport Adapter - USB-C Mini Travel Dock w/ 4K HDMI or 1080p VGA - 3x USB 3.0 Hub, SD, GbE, Audio, 100W PD Pass-Through - Portable Docking Station for Laptop/Tablet

**Product ID:** DKT30CHVAUSP



This USB-C multiport adapter turns your MacBook Pro, USB-C laptop, Chromebook, or Android (Samsung Galaxy S8, Note 9 and above) device into a workstation, anywhere you go. A USB Type-C adapter, ideal for travel, features everything from the essential HDMI or VGA video outputs and USB ports to an SD card reader and 100W PD including PD passthrough. All through a single extended length 30 cm, Thunderbolt 3 or USB-C attached host cable, providing more flexibility for harder to reach laptop and tablet connections.

To ensure full adapter functionality, your laptop's USB-C port must support USB Power Delivery and DP Alt Mode.

This USB-C multiport adapter features both an HDMI and VGA port providing you with two single video output options for your boardroom presentations or your workstation setup including support for an ultra-wide monitor.

With support for USB PD 3.0 (up to 100W), the USB Type-C multiport adapter lets you power and charge your laptop, and power your peripherals when connected to a USB-C power adapter. The USB-C hub features PD passthrough so you can use your laptop's own charger to power the hub (requires 15W) and power or charge your laptop simultaneously.

The USB-C to USB 3.0 hub gives you one USB-C port (power & data) and two USB-A ports to connect your latest and legacy USB devices.

Access your multimedia content, audio, and network with ease. The multiport adapter provides direct access to your:

- SD, SDHC and SDXC memory cards or microSD cards via the SD card slot
- Audio content via headphones or microphone through the 3.5mm 4- position audio port
- Ethernet network via the GbE port using a hard-wired connection

DKT30CHVAUSP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Seamlessly create a familiar and productive workstation wherever you travel
- Creative professionals can use the built-in card reader to access multimedia

### Features

- **8-IN-1 MULTI PURPOSE DOCK:** USB-C multiport adapter eliminates the need for multiple adapters w/ 4K30Hz HDMI or 1080p VGA, 5Gbps USB (2x USB-A, USB-C), SD slot, Gigabit Ethernet, headset/mic audio jack
- **100W POWER DELIVERY 3.0:** Use your laptop's USB-C power adapter to power the dock and provide up to 85W to power & charge your laptop, w/ 15W always reserved for the USB type-c travel dock hub
- **EXTRA LONG CABLE:** 1ft (30cm) attached cable on this usb-c mini dock for extended reach to reduce port/connector strain on 2-in-1 devices like Surface Pro 7, iPad Pro, HP Elite & laptop on riser stands
- **WIDE DEVICE COMPATIBILITY:** Compatible w/ USB-C & Thunderbolt 3 laptops, tablets, or smartphones, this portable USB-C docking station works w/ HP, Lenovo, Dell, MacBook, Chromebook & Samsung Galaxy
- **WIDE OPERATING SYSTEM COMPATIBILITY:** With automatic driver setup, this all-in-one USB-C multiport adapter supports all major operating systems, including Windows, macOS, ChromeOS, iPadOS and Android

---

#### Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	1
Ports	7
Audio	Yes
Bus Type	USB 3.1 Gen 1
Port Style	Cable Adapters
Chipset ID	VIA Labs - VL102
	VIA Labs - VL161
	VIA Labs - VL817

Genesys Logic - GL823K

ITE Tech - IT6564

Realtek - RTL8153B

Cmedia - HS100-B

---

## Performance

Maximum Cable Length	11.8 in [30 cm]
Maximum Analog Resolutions	1920 x 1200 @ 60Hz (VGA)
Maximum Digital Resolutions	3840 x 2160 @30Hz, 4096 x 2160 @24hz, 3440 x 1440 @60Hz (HDMI)
Audio Specifications	3.5mm Audio
Type and Rate	USB 3.1 Gen 1 - 5 Gbit/s
Compatible Networks	10/100/1000 Mbps
General Specifications	Power Reservation: 15W
MTBF	372518 hours

---

## Connector(s)

External Ports	HDMI
	VGA (15 pin, High Density D-Sub)
	RJ-45
	USB 3.1 USB Type-A (9 pin, Gen 1, 5 Gbps)
	SD Slot
	3.5 mm Audio
	3.5 mm Audio
Host Connectors	USB Type-C (24 pin) USB 3.0 (5Gbps)
	USB Type-C (24 pin) USB 3.0 (5Gbps)

---

## Software

OS Compatibility	macOs Big Sur (11.0) macOS Catalina (10.15), macOS Mojave
------------------	---

(10.14), macOS High Sierra (10.13), macOS Sierra (10.12), Mac OS X El Capitan (10.11), iOS, Windows 10, Windows 8.1, Windows 8, Windows 7, Chrome OS, Android

---

**Power**

Power Source	Not Included (not required for standard applications)
Power Delivery	100W
Laptop Charging via Power Delivery	

---

**Environmental**

Operating Temperature	0~45C
Storage Temperature	-10~82C
Humidity	5%~90%

---

**Physical Characteristics**

Color	Black & Space Gray
Material	Aluminum and Plastic
Cable Length	11.8 in [30 cm]
Product Length	18.1 in [46.0 cm]
Product Width	2.4 in [61.0 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	4.4 oz [125.0 g]

---


**Packaging Information**

Package Length	6.7 in [17.0 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	6.7 oz [190.0 g]

---

**What's in the Box**

Included in Package	USB-C Docking Station
---------------------	-----------------------



Quick-Start Guide

---

***\*Product appearance and specifications are subject to change without notice.***

