

DisplayPort to DVI Video Adapter Converter

Product ID: DP2DVI2

The DP2DVI2 DisplayPort to DVI Video Adapter Converter lets you connect a DVI monitor to DisplayPort-enabled desktop or laptop computers.

Supporting display resolutions of up to 1920x1200 allowing you to take full advantage of single link DVI capability. DP2DVI2 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

StarTech.com also offers the DP2DVIS, an Active DisplayPort to DVI adapter.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Keep your existing DVI monitor to be used with your new DisplayPort device
- Ideal for using your DVI monitor as a secondary display

Features


- Latching DisplayPort connector ensures a solid connection
- Easy to use cable, no software required
- Supports PC resolutions up to 1920x1200 and HDTV resolutions up to 1080p

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	DisplayPort - 1.2
AV Output	DVI-I (Digital Only) - Single-Link
Audio	No

Performance

Maximum Digital Resolutions	1920x1200 / 1080p
-----------------------------	-------------------



Supported Resolutions	1920x1080 (1080p)
	1680x1050 (WSXGA+)
	1600x1200
	1600x900
	1440x900
	1400x1050 (SXGA+)
	1366x768
	1360x768
	1280x1024
	1280x960
	1280x800
	1280x768 (WXGA)
	1280x720p (720p)
	1280x600
	1152x864
	1024x768
	800x600 (SVGA)
	640x480 (480p)

Wide Screen Supported	Yes
Audio Specifications	DVI - No Audio Support

Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DVI-I (29 pin)

Special Notes / Requirements

System and Cable Requirements	DP++ port (DisplayPort ++) required on video card or video source (DVI and HDMI pass-through must be supported)
-------------------------------	---

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 80C (14F to 176F)



Humidity	10%-85%RH
----------	-----------

Physical Characteristics

Color	Black
Cable Length	6.0 in [15.2 cm]
Product Length	10.0 in [25.4 cm]
Product Width	1.7 in [42.0 mm]
Product Height	0.7 in [17.0 mm]
Weight of Product	1.5 oz [43.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.7 in [19.0 mm]
Shipping (Package) Weight	1.8 oz [52.0 g]

What's in the Box

Included in Package	DisplayPort to DVI Converter
---------------------	------------------------------

****Product appearance and specifications are subject to change without notice.***

