

USB C Multiport Adapter - Portable USB-C Mini Dock 4K HDMI Video - Gigabit Ethernet, USB 3.0 Hub (1x USB-A 1x USB-C) - USB Type-C Multiport Adapter - Thunderbolt 3 Compatible

**Product ID:** DKT30CHD



This USB-C Multiport Adapter with HDMI combines the capability of three single-function adapters, a USB-C video adapter, USB-C to USB 3.0 adapter, and Gigabit Ethernet adapter, into a portable docking station for your laptop. You can connect a 4K HDMI display and two USB 3.0 devices (1x USB-A, 1x USB-C), and get high-speed network access, all through a single cable.

The USB Type-C adapter is compatible with Thunderbolt 3 ports.

With HDMI output, this USB-C multiport adapter makes it easy to expand your virtual workspace onto an external 4K HDMI monitor. The adapter supports resolutions up to 4096 x 2160p (24Hz) or 3840 x 2160p (30Hz), as well as audio.

The USB-C multiport adapter ensures a reliable wired network connection with a Gigabit Ethernet port, which is ideal for areas with limited Wi-Fi access such as in classrooms, office buildings and hotels.

With two USB 3.0 ports (1x USB-A, 1x USB-C) you get access to traditional USB Type-A devices, as well as newer USB-C devices you add in the future.

With its compact design and bus-powered performance, the portable multiport adapter is easy to take with you anywhere you take your laptop. The adapter features a pre-attached USB-C cable, so you have one less cable to carry when you're on the move.

- Maximum compatibility - StarTech.com has a docking station to fit every operating system, laptop brand, and connectivity need

Get more done faster - More ports and more displays maximize end user connectivity and productivity

Quick installation - eliminate deployment headaches that waste time and frustrate end users

IT Grade quality - trusted by IT pros around the world for our rigorous in-house product testing, robust compliance, and lifetime multilingual technical support

The DKT30CHD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Note: Your USB-C equipped host laptop must support video (DP Alt Mode) to work with this adapter. The adapter does not support USB Power Delivery.

## Certifications, Reports and Compatibility

### Applications

- Ideal for mobile use
- Integrate into small workspaces in offices and home offices

### Features

- **DOCKING STATION WITH ESSENTIAL PORTS:** 4-in-1 USB C multiport adapter with 4K 30Hz HDMI video output, Gigabit Ethernet port, USB 3.0 Hub 5Gbps (1x USB-A and 1x USB-C ports); USB bus-powered
- **EXTRA LONG CABLE:** Mini dock has an attached 13 in (34cm) cable to provide extended reach to reduce connector strain on 2-in-1 devices like Surface Pro 7, iPad Pro, HP Elite or laptops on riser stands
- **DESIGNED FOR PORTABILITY:** USB-C port expander w/ ultra compact square design for presentations in meeting rooms connected to a TV/display/monitor, working from home or on the go
- **WIDE DEVICE COMPATIBILITY:** USB-C and Thunderbolt 3 laptops, ultrabooks, USB-C Chromebook, tablets and phones for brands such as HP, Dell, Lenovo, MacBooks, iPad Pro, Surface, Samsung and Pixelbook
- **WIDE OS COMPATIBILITY & EASY SETUP:** Universal USB Type-C multiport adapter features automatic driver installation & supports major operating systems like Windows, macOS, Chrome OS, iPadOS and Android

---

#### Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	1
Bus Type	USB-C
Chipset ID	Genesys Logic - GL3523 Realtek - RTL8153 Parade - PS176

---

**Performance**

Maximum Data Transfer Rate	5 Gbps (USB 3.0) <br / >2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	4096 x 2160p @ 24Hz or 3840 x 2160p (HDMI) @ 30Hz
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

---

**Connector(s)**

Connector Type(s)	USB Type-C (24 pin) USB 3.0 (5Gbps)
	HDMI (19 pin)
	RJ-45
	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	USB Type-C (24 pin) USB 3.0 (5Gbps)

---

**Software**

OS Compatibility	Windows 7, 8, 8.1, 10
	macOS 10.10 to 10.15, 11.0
	Chrome OS

---

**Special Notes / Requirements**

System and Cable Requirements	Host laptop with an available USB-C port (to ensure full functionality, the laptop's USB-C port must support DP alt mode).
Note	<p>Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your laptop USB-C port supports DP alt mode.</p> <p>A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K).</p> <p>USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.</p>



The USB Type-C connector (female) is data only.

---

**Power**

Power Source	USB-Powered
--------------	-------------

---

**Environmental**

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	5~90% RH (Non-condensing)

---

**Physical Characteristics**

Color	Black
Material	Plastic
Cable Length	13.4 in [34 cm]
Product Length	2.6 in [65 mm]
Product Width	2.4 in [62 mm]
Product Height	0.6 in [15 mm]
Weight of Product	1.8 oz [52 g]

---

**Packaging Information**

Package Length	8.3 in [21 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.6 in [40 mm]
Shipping (Package) Weight	5.9 oz [168 g]

---

**What's in the Box**

Included in Package	USB-C multiport adapter
	quick-start guide

---

*\*Product appearance and specifications are subject to change without notice.*