

12ft (4m) VESA Certified DisplayPort 1.4 Cable - 8K 60Hz HBR3 HDR - Super UHD DisplayPort to DisplayPort Monitor Cord - Ultra HD 4K 120Hz DP 1.4 Slim Video Cable M/M DP Connector

Product ID: DP14MM4M



This DisplayPort 1.4 cable connects your DisplayPort laptop or desktop computer to a “super ultra-high definition” 8K monitor, TV or projector. It supports resolutions up to 8K (7680x4320) @ 60Hz.

The DP monitor cable provides the essential connection to support the next generation of super ultra-high definition video.

This 4m VESA certified DisplayPort cable ensures full compliance and efficient operation of the higher link rate of HBR3. This DP cord has been tested to meet all DP 1.4 specifications to ensure quality and reliability.

This 8K DisplayPort cable supports all DP 1.4 features:

- High Bit Rate 3 (HBR3) Bandwidths of 32.4 Gbps supporting the latest in industry standards
- High Dynamic Range (HDR) for higher contrast ratio and vivid colors
- Multi-Stream Transport (MST) for daisy-chaining multiple monitors
- Display Stream Compression 1.2 (DSC) for maximum resolution output
- Forward Error Correction to manage data transmission errors
- High-Bandwidth Digital Content Protection (HDCP 2.2) for a secure connection between source and display
- 32 Uncompressed Digital Audio Channels

The cable has a slim professional grade 28 AWG construction that allows for flexible installation while offering superior reliability for a clean quality installation. Each connector features latches that provide secure connections between your devices.

8K has a resolution of 7680 x 4320 and is also known as 4320p and Super Ultra High Definition (SUHD). It is seen in

digital signage and other commercial displays that require the highest available resolution. This cable is backward compatible with 4K and 5K displays making it the perfect peripheral to start future-proofing your cabling infrastructure.

DP14MM4M is backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Delivering visually enriched presentations
- Displaying crisp digital signage walls
- Creating eye-catching visuals for photography, videography, cinematography
- Producing lifelike gaming

Features


- **DISPLAYPORT 1.4 CABLE:** 13.12 foot (4 meter) cable, VESA Certified w/32.4Gbps bandwidth; 8K 60Hz (7680x4320), 4K 120Hz (3840x2160), HDR for high contrast ratio, HBR3, 32 ch audio, MST for monitor daisy-chain, FEC error control
- **RELIABLE:** Built with internal wire manager to ensure signal integrity; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **DURABLE:** PVC jacket of this slim video cable absorbs stress of frequent bends protecting the core of the DisplayPort cord; Gold plated connectors prevent oxidization and tarnish, Lifetime Warranty
- **APPLICATIONS:** Ideal for professional workstations w/Radeon Vega Frontier/Pro WX Series/W5500/Pro Duo & Nvidia Quadro; Compatible w/DP 1.1/1.2/1.3 (1080p/4K) cards & adapters to future-proof for 8K
- **SPECS:** 4 m (13.1 ft) Black DisplayPort 1.4 DP Male to Male 28 AWG Jacket: PVC EMI Shielding Supported Protocols: HBR 3, 4:4:4 Chroma Subsampling, DSC 1.2, HDCP 2.2, MST Lifetime Warranty

Prominence

	Warranty	Lifetime
Description	CDW 75 - 1st Line	StarTech.com 13' 4m VESA Certified DisplayPort 1.4 Cable w/Latches DP 8K/4K

Hardware

Number of Conductors	19
Connector Plating	Gold



Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	VW-1 Rated

Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	28 AWG
Cable Length	13.1 ft [4 m]
Product Length	13.1 ft [4 m]
Product Width	0.7 in [19 mm]
Product Height	0.5 in [12 mm]
Weight of Product	11.6 oz [328 g]

Packaging Information

Package Length	12.9 in [32.7 cm]
Package Width	9.8 in [25 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	12.2 oz [346 g]

What's in the Box

Included in Package	DisplayPort Cable
---------------------	-------------------

**Product appearance and specifications are subject to change without notice.*

