

6 ft DisplayPort to DVI Cable - M/M

Product ID: DP2DVI2MM6

The DP2DVI2MM6 6 ft DisplayPort to DVI Adapter Cable lets you connect a DVI Display or Projector to a DisplayPort video card/source. Providing a connection distance of 6ft, the cable features male DVI and DisplayPort connectors, allowing you to make a direct video card-to-display connection, as opposed to having to use an adapter with a separate cable.

The DP to DVI cable is a convenient, cost-effective solution for taking full advantage of your DVI display, without the expense of upgrading to a DisplayPort monitor. The cable offers high quality construction and supports high bandwidth video resolutions up to 1920x1200 or HDTV resolutions up to 1080p.

DP2DVI2MM6 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port. Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Re-purpose an existing DVI display for use with a new DisplayPort-equipped computer, or as a secondary display
- Connect a DisplayPort video source directly to any DVI-D (digital) display with no additional adapters required
- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays

Features

- All-in-one cable design
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- No software or additional drivers required
- Latching DisplayPort connector port

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	DisplayPort - 1.2
AV Output	DVI-D - Single-Link
Audio	No

Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Maximum Digital Resolutions	1920x1200 / 1080p
Audio Specifications	DVI - No Audio Support

Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DVI-D (25 pin)

Special Notes / Requirements

Note	DP++ (DisplayPort++) port is required on video card or video source for DVI and HDMI pass-through.
------	--

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10%-85%RH

Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.6 in [40.0 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	5.0 oz [143.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.2 in [31.0 mm]



Shipping (Package) Weight	5.4 oz [152.0 g]
------------------------------	------------------

**What's in the
Box**

Included in Package	6 ft DisplayPort to DVI Cable - M/M
---------------------	-------------------------------------

****Product appearance and specifications are subject to change without notice.***

