

6ft (1.8m) DisplayPort to DVI Cable, DisplayPort to DVI Adapter Cable, Passive DP to DVI-D Video Converter, 1080p - Replacement for DP2DVIMM6

Product ID: DP2DVI2MM6



The DP2DVI2MM6 6 ft DisplayPort to DVI Adapter Cable lets you connect a DVI Display or Projector to a DisplayPort video card/source. Providing a connection distance of 6ft, the cable features male DVI and DisplayPort connectors, allowing you to make a direct video card-to-display connection, as opposed to having to use an adapter with a separate cable.

The DP to DVI cable is a convenient, cost-effective solution for taking full advantage of your DVI display, without the expense of upgrading to a DisplayPort monitor. The cable offers high quality construction and supports high bandwidth video resolutions up to 1920x1200 or HDTV resolutions up to 1080p.

DP2DVI2MM6 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port. Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect a DisplayPort video source directly to any DVI-D (digital) display with no additional adapters required
- Re-purpose an existing DVI display for use with a new DisplayPort-equipped computer, or as a secondary display
- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays

Features

- **DISPLAYPORT TO DVI CABLE:** 6ft (1.8m) DisplayPort 1.2 (HBR2) to DVI-D single-link cable connects a DVI display, monitor or projector, 1920x1200/1080p 60Hz or 4K 30Hz (HDMI clock rate); HDCP 1.4, EDID ensures compatibility between source & display
- **COMPATIBILITY:** Passive video converter supports DP++ sources including workstations, desktops (AMD/Nvidia), laptops, small form factor computers & docking stations
- **INTEGRATED DISPLAY CABLE:** DisplayPort to DVI adapter cable has slim & flexible design w/ adapter chip built into DVI connector reducing clutter & providing a tidy install in the office, boardroom or home office
- **LATCHING DISPLAYPORT & SCREW LOCKING DVI:** Latching DP connector & gold plated DVI connector ensure solid connection; Chip built into DVI connector minimizes signal loss Supports DVI screw locking cable to prevent cable accidental disconnection
- **EASY TO USE:** With no software or drivers required, the DP to DVI cable/cord works with any OS including Windows, Ubuntu and macOS; DisplayPort male to DVI male cable; A direct replacement for DP2DVIMM6

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	DisplayPort - 1.2
AV Output	DVI-D - Single-Link
Audio	No
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Maximum Digital Resolutions	1920x1200 / 1080p
Audio Specifications	DVI - No Audio Support

Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DVI-D (25 pin)

Special Notes / Requirements

Note	DP++ (DisplayPort++) port is required on video card or video source for DVI and HDMI pass-through.
------	--

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10%-85%RH

Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.6 in [4.0 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	5.0 oz [143.0 g]

Packaging Information

Package Quantity	1
Package Length	5.7 in [14.6 cm]
Package Width	7.2 in [18.3 cm]
Package Height	1.7 in [4.4 cm]
Shipping (Package) Weight	5.7 oz [162.0 g]

What's in the Box

Included in Package	1 - 6 ft DisplayPort to DVI Cable - M/M
---------------------	---

****Product appearance and specifications are subject to change without notice.***