

## DisplayPort to DVI Active Adapter

### Product ID: DP2DVIS

The DP2DVIS DisplayPort to DVI Active Single Link adapter lets you connect your DisplayPort video source (desktop PC, laptop, etc.) to a DVI-D monitor, projector or display, including televisions and Apple Cinema Display HD, eliminating the expense of having to upgrade to a DisplayPort-capable monitor.

Unlike passive adapters, this DP to DVI converter offers an active conversion for use with any DisplayPort output - ideal for graphics cards that are not capable of outputting multi-mode DP++ signals (e.g. ATI Eyefinity). Supporting resolutions up to 1920x1200, this compact device provides a simple solution for converting DisplayPort output for compatibility with existing DVI monitors, televisions or projectors.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Great for using your DVI monitor as a secondary display
- Keep your existing DVI monitor to be used with your new DisplayPort computer or source
- Perfect for larger format screens that use high DVI resolutions
- Adapt from graphics cards that are not capable of outputting DP++ (multi-mode) signals

### Features

- Latching DisplayPort connector
- Compliant with DisplayPort 1.1a specifications
- Supported on any DVI-D display including televisions and Apple Cinema Display HD
- Supports HDCP 1.3
- Supports resolutions up to 1920x1200
- Works with video cards not capable of outputting DP++ (multi-mode) signals

---

#### Hardware

Warranty 3 Years

Active or Passive Adapter Active



AV Input	DisplayPort - 1.2
AV Output	DVI-D - Single-Link
Audio	No
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Industry Standards	HDCP 1.3 DisplayPort 1.1a DDWG 1.0

---

#### Performance

Maximum Digital Resolutions	1920x1200
Wide Screen Supported	Yes
Audio Specifications	DVI - No Audio Support

---

#### Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DVI-D (25 pin)

---

#### Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	80~90% RH

---

#### Physical Characteristics

Color	Black
Cable Length	5.7 in [14.6 cm]
Product Length	7.9 in [20 cm]
Product Width	1.7 in [44 mm]
Product Height	0.8 in [20 mm]
Weight of Product	1.7 oz [48 g]

---

#### Packaging



**Information**

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.8 in [20 mm]
Shipping (Package) Weight	2.0 oz [57 g]

---

**What's in the Box**

Included in Package	DisplayPort to DVI Adapter
---------------------	----------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

