

DisplayPort to VGA Video Adapter Converter

Product ID: DP2VGA2

This DisplayPort to VGA adapter lets you connect your DP computer to a VGA monitor or projector. The adapter works with DisplayPort computers like your HP Elitebook Revolve 810 G3.

The DP to VGA adapter lets you connect your DisplayPort laptop or desktop computer to a VGA display. The adapter supports plug-and-play connectivity ensuring a hassle-free setup.

The DisplayPort adapter makes your DP computer fully compatible with existing VGA monitors or projectors in your home or around your office. The VGA connector features nuts that mate with the screws on standard VGA cables, to ensure your video cable won't get disconnected.

The DisplayPort to VGA converter maximizes portability with a compact, lightweight design, making it the perfect travel accessory to carry with your DisplayPort laptop, fitting easily into your laptop bag or carrying case. This ultra-portable design makes this adapter perfect for BYOD (Bring Your Own Device) applications at the office.

With support for video resolutions up to 1920x1200 or 1080p, you'll be surprised at the picture quality the adapter provides, even when connected to a legacy VGA monitor, projector or television. The adapter harnesses the video capabilities built into your DP connection to deliver every detail in stunning high-definition.

The DP2VGA2 is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Keep the adapter with you while you're traveling, to connect to VGA displays at trade shows or in hotel rooms
- Connect your BOYD laptop to a VGA office hot desk or boardroom projector
- Use your VGA monitor as a secondary display

Features

- Maximum portability with a small footprint and lightweight design
- Hassle-free connectivity with plug-and-play DP to VGA video adapter
- Crystal clear picture quality with support for high-definition video resolutions up to 1920x1200 or 1080p

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	DisplayPort - 1.2



AV Output VGA

Audio No

Performance

Maximum Analog Resolutions 1920x1200

Wide Screen Supported Yes

Audio Specifications VGA - No Audio Support

Connector(s)

Connector A DisplayPort (20 pin)

Connector B VGA (15 pin, High Density D-Sub)

Environmental

Operating Temperature 0C to 45C (32F to 113F)

Storage Temperature -10C to 80C (14F to 176F)

Humidity 10%-85%RH

Physical Characteristics

Color Black

Material Plastic

Cable Length 8.9 in [22.5 cm]

Product Length 11.0 in [27.9 cm]

Product Width 1.4 in [35.0 mm]

Product Height 0.8 in [20.0 mm]

Weight of Product 1.5 oz [43.0 g]

Packaging Information

Package Length 8.7 in [22.0 cm]

Package Width 7.9 in [20.0 cm]

Package Height 0.8 in [21.0 mm]



Shipping (Package) Weight	1.8 oz [52.0 g]
------------------------------	-----------------

**What's in the
Box**

Included in Package	DisplayPort to VGA Converter
---------------------	------------------------------

****Product appearance and specifications are subject to change without notice.***

