

15ft (4.6m) DisplayPort to VGA Cable - Active DisplayPort to VGA Adapter Cable - 1080p Video - DP to VGA Monitor Cable - DP 1.2 to VGA Converter - Latching DP Connector

Product ID: DP2VGAMM15B



The DP2VGAMM15B 15ft active DisplayPort to VGA converter cable lets you connect your DisplayPort-equipped desktop or laptop directly to a VGA monitor or projector at a longer distance than a standard-length cable would support, while saving the expense of additional adapters.

Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The DP2VGAMM15B is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (Desktop, Laptop computer)
- Use your VGA monitor as a secondary display, connected to a DisplayPort output
- Connect a DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting

Features

- **DISPLAYPORT TO VGA CABLE:** 15ft (4.6m) DisplayPort 1.2 (HBR2) adapter cable lets you connect a single VGA display supporting 2048x1280, 1920x1200 & 1920x1080 (1080p) at 60Hz; EDID & DDC pass-through ensure compatibility between source & display
- **COMPATIBILITY:** Active digital to analog converter supports DP or DP++ source w/ standard DP connector incl workstations, desktops (AMD/Nvidia), laptops, small form factor computers & docking stations
- **INTEGRATED DISPLAY CABLE:** Adapter cable has slim & flexible design w/ adapter chip built into VGA connector reducing clutter & providing a tidy install in the office, boardroom or home office; 15' length supports longer distance than traditional VGA cable
- **LATCHING DISPLAYPORT & SCREW LOCKING VGA:** Latching DP connector ensures a solid host connection, and chip built into VGA connector minimizes signal loss. Supports VGA screw locking cable to prevent cable from coming loose or accidental disconnection
- **EASY TO USE:** With no software or drivers required, the DP to VGA video converter cable/cord works with any OS including macOS, Windows & Ubuntu. DP Source to VGA Monitor/Display/Projector DisplayPort Male to VGA Male Cable

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	DisplayPort - 1.2
AV Output	VGA
Audio	No
Chipset ID	Analogix - 9832

Performance

Maximum Cable Length	15.0 ft [4.6 m]
Maximum Analog Resolutions	1920x1200 / 1080p (Output)
Maximum Digital Resolutions	1920x1200 / 1080p (Input)
Audio Specifications	VGA - No Audio Support
MTBF	1,449,804 hours

Connector(s)

Connector A	1 - DisplayPort (20 pin)
-------------	--------------------------

Connector B	1 - VGA (15 pin, High Density D-Sub)
-------------	--------------------------------------

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40%-85%RH

Physical Characteristics

Color	Black
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]
Product Width	1.6 in [4 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	7.7 oz [218 g]

Packaging Information

Package Quantity	1
Package Length	9.4 in [24 cm]
Package Width	6.3 in [16 cm]
Package Height	0.8 in [20 mm]
Shipping (Package) Weight	6.2 oz [175 g]

What's in the Box

Included in Package	1 - DisplayPort to VGA Adapter Cable
---------------------	--------------------------------------

**Product appearance and specifications are subject to change without notice.*