

Black Aluminum 5.25in Rugged SATA Hard Drive Mobile Rack Drawer

Product ID: DRW150SATBK



This high quality Removable SATA Hard Drive Drawer/Mobile Rack delivers a professional-grade hot-swap solution, allowing you to quickly swap SATA hard drives in/out of a computer without having to open the computer case. The mobile rack is fully compatible with RAID installations to ensure maximum performance and versatility for enhanced storage applications.

To maximize performance and utilize the full speed potential of your SATA III hard drives, this HDD Backplane supports SATA III for transfer speeds up to 6 Gbps when paired with a compatible controller.

Simply install the drive bay into a 5.25in bay on the host computer, then mount a 3.5in SATA HDD into the (removable) caddy. Connecting the SATA hard drive to the computer is as easy as inserting the caddy into the drive bay, which can be locked to prevent unauthorized removal of the drive. Features a front panel ball bearing fan, aluminum construction and 25K insertion rating. Backed by StarTech.com's 2-year warranty.

Certifications, Reports and Compatibility



Applications

- Add additional hot-swap bays to a server or workstation computer
- Replace or upgrade old IDE backplane with a SATA backplane
- System builders who need to image many drives simultaneously and quickly
- Environments where drives need to be replaced/removed regularly, without external protection for the drives required after removal
- Be able to replace/remove individual drives from a storage array with minimal or no system down time

Features

- Fits a single SATA drive into a front accessible 5.25" bay
- Heavy duty aluminum construction for the drive caddy and bay
- Key lockable drive caddy
- Rubber shock absorbers
- 25,000+ insertion rating
- 40mm ball bearing cooling fan
- Dust resistant door on bay unit
- Power and Activity LED indicators
- Support for SATA revision I/II/III (1.5/3.0/6.0 Gbps)
- Supports 3.5" form factor SATA hard drives

Hardware	Warranty	2 Years
	Front Door Key Lock	Yes
	Fans	40 mm
	Drive Size	3.5in
	Compatible Drive Types	SATA
	Fan Bearing Type	Ball Bearing
Connector(s)	Drive Connectors	SATA (7 pin, Data)
	Drive Connectors	SATA Power (15 pin)
	Host Connectors	SATA (7 pin, Data)
	Host Connectors	SATA Power (15 pin)
	Host Connectors	LP4 (4 pin; Large Drive Power)
Software	OS Compatibility	OS independent; No software or drivers required
Special Notes / Requirements	System and Cable Requirements	PC or Mac with a 5.25 Inch Drive Bay
	Note	Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated
Indicators	LED Indicators	Power (Green)
	LED Indicators	Activity (Yellow)
Physical Characteristics	Color	Black
	Material	Aluminum
	Product Length	7.5 in [1.9 cm]
	Product Width	5.8 in [1.5 cm]
	Product Height	1.6 in [41 mm]

Weight of Product 27.6 oz [782 g]

Packaging Information

Package Length 7.7 in [2.0 cm]
Package Width 6.0 in [1.5 cm]
Package Height 1.9 in [47 mm]
Shipping (Package) Weight 29.4 oz [834 g]

What's in the Box

Included in Package 5.25" Mobile Rack Bay
Included in Package Instruction Manual
Included in Package SATA Cable
Included in Package Mobile Rack Caddy
Included in Package Screw Kit
Included in Package Key

****Product appearance and specifications are subject to change without notice.***

