

15ft 4-in-1 USB Dual Link DVI-D KVM Switch Cable w/ Audio & Microphone

Product ID: DVID4N1USB15



The DVID4N1USB15 15ft 4-in-1 USB Dual Link DVI-D KVM Switch Cable w/ Audio & Microphone integrates dual link DVI video quality with USB mouse and keyboard, 3.5mm audio out and microphone connections into a single, compact cable.

The four-in-one DVI KVM cable is a cost-effective and convenient solution that's suitable for use with dual link DVI supported USB KVM switches, allowing you to share a USB peripheral set between two computers configured for high definition output.

Backed by a StarTech.com Lifetime Warranty.

Works with:
Compatible StarTech.com KVMs can be found under the Accessories section.
Aten models (CS1642, CS1644, CS1784, CS1782, CS1762, CS1764)
Avocent models (2SVDVI10-001, 4SVDVI10-001, SV4UAD, SC420, SC440, SC540)
Belkin models (F1DN102D, F1DN104D, F1DD102L, F1DD104L)
Cables to go models (52047, 52048)

Certifications, Reports and Compatibility



Applications

- Connects a computer to a Dual Link DVI + USB KVM switch with audio and mic support

Features

- Combines 4 peripheral cables into one
- Dual Link DVI-D signal is supported

- Meets and exceeds all DVI-D and USB 2.0 specifications
- Supports DVI-D Maximum clock frequency in dual link mode up to 7.92 Gbit/s)

Hardware	Warranty	Lifetime
	Cable Jacket Material	PVC - Polyvinyl Chloride
Connector(s)	Connector A	DVI-D (25 pin)
	Connector A	3.5 mm Mini-Jack (3 Position)
	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	DVI-D (25 pin)
	Connector B	3.5 mm Mini-Jack (3 Position)
	Connector B	USB B (4 pin)
Physical Characteristics	Color	Black
	Cable Length	15.0 ft [4.6 m]
	Product Length	15.0 ft [4.6 m]
	Product Width	1.6 in [39.5 mm]
	Product Height	0.6 in [15.5 mm]
	Weight of Product	31.2 oz [885 g]
Packaging Information	Package Length	12.8 in [3.2 cm]
	Package Width	9.8 in [2.5 cm]
	Package Height	2.8 in [70 mm]
	Shipping (Package) Weight	31.2 oz [885 g]
What's in the Box	Included in Package	4-n-1 DVI-D USB KVM Cable

**Product appearance and specifications are subject to change without notice.*

