

Dual SATA to LP4 Power Doubler Cable Adapter – 2 SATA to 4 Pin LP4 Internal PC Peripheral Power Supply Connector – SATA Y Cable – Male/Female – 18 AWG Wire – 9 Amps/108W

**Product ID:** DSATPMOLP4



The SATA power to LP4 power cable adapter features two male SATA power connectors and one female LP4 power connector.

The pc internal power cable eliminates the need to upgrade your power supply for peripherals that require additional power via the LP4 connector. This enables you to extend your power connections and allows you to position your internal PC devices (i.e. hard drive, DVD-ROM drive, add-in card, etc.) inside the system case. In addition, the dual SATA power cable offers 6-inches in cable length from each of the SATA connector to the 4 pin LP4 peripheral power connector.

Constructed of only top-quality materials and designed for optimum performance and reliability, this power supply SATA cable is the perfect connectivity solution for demanding devices.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The DSATPMOLP4 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## **Certifications, Reports and Compatibility**

### **Applications**

- Provides flexibility in LP4 device and cable placement when building or upgrading systems
- Extend the connection distance of your 4 pin LP4 devices by 6 inches from your SATA power

## Features

- **DUAL SATA TO LP4 POWER CABLE:** This power supply doubler adapter cable overcomes SATA Power supply (ATX) output limits by combining 2 SATA power connections into one 4-Pin LP4 connector, providing extra power to drive backplanes & storage peripherals
- **DUAL SATA PROVIDES 150W TO LP4 DEVICE:** Dual SATA Power inputs provide additional 5V and 12V power lines, providing extra 4.5A current per line, giving a total power output of 108W (9A at 12V) and 45W (9A at 5V)
- **EXTRA POWER FOR 4-Pin LP4 BACKPLANES:** The double SATA power supply to LP4 adapter cable provides extra power to mobile rack multi-drive (SSD/HDD) Backplanes that utilize LP4 Power such as StarTech.com SATSASBP425
- **HIGH QUALITY CONSTRUCTION:** 100% copper 18AWG UL1007 wires with PVC insulation, allowing max current of 4.5A per wire, Insulation tested upto 300V DC and connectors made from high strength LD-PE that can withstand high voltage and current ratings
- **SPECS:** 6 inch 2x SATA Power male to LP4-Pin female Insulation: PVC Connector: LD-PE 18 AWG, UL1007 Lifetime Warranty Note: Connected LP4 device must not draw more than 153W (9A per line)

---

### Connector(s)

	Warranty	Lifetime
Connector A		SATA Power (15 pin)
Connector B		LP4 (4 pin; Large Drive Power)

---

### Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (32F to 158F)
Humidity	Humidity: 0% to 95% RH (non-condensing) at 25C

---

### Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	5.9 in [15 cm]
Product Length	7.5 in [19.1 cm]
Product Width	1.1 in [29.0 mm]
Product Height	0.1 in [1.5 mm]

Weight of Product	1.1 oz [32.0 g]
-------------------	-----------------

---

**Packaging Information**

Package Length	7.7 in [19.5 cm]
----------------	------------------

Package Width	5.0 in [12.8 cm]
---------------	------------------

Package Height	0.3 in [7.4 mm]
----------------	-----------------

Shipping (Package) Weight	1.0 oz [27.0 g]
---------------------------	-----------------

---

**What's in the Box**

Included in Package	Dual SATA to LP4 Adapter
---------------------	--------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

