

6 ft 90° Upward Angled Dual Link DVI-D Monitor Cable - M/M

Produkt ID: DVIDDMMTA6



The DVIDDMMTA6 6ft Dual Link DVI-D cable features a standard DVI-D dual link connector as well as a DVI-D dual link connector that is situated on an upward angle relative to the shaft of the cable, requiring only 40mm of space at the connection point.

The perfect solution for making digital video connections in tight spaces, the design of the upward angle cable connector helps prevent damage to the cable and ensures long-lasting performance by eliminating the need to bend or strain the cable to account for a lack of space.

The 6ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector, even in tight spaces

Funktioner

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- 90° Upward Angled connector with a 40mm depth

Hårdvara

Garantipolicy	Lifetime
Kabelmanteltyp	PVC - Polyvinyl Chloride
Industristandarder	DVI DDWG Standard

Kontakt(er)

Connector A	1 - DVI-D (25-stifts)
Connector B	1 - DVI-D (25-stifts)

Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	6.0 ft [1.8 m]
Yttre kabeldiameter	0.3 in [8.6 mm]
Produktlängd	6.0 ft [1.8 m]
Produktvikt	7.7 oz [218 g]

Förpackning

Förpackningsantal	1
Paketets längd	7.9 in [20 cm]

Paketets bredd	0.0 in [1 mm]
Paketets höjd	8.3 in [21 cm]
Fraktvikt (förpackning)	0.5 lb [0.2 kg]

Vad det är i lådan

Ingår i paketet	1 - 6ft Up Angled DVI-D Dual Link Digital Monitor Cable
-----------------	---

Warranty
Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.