

6ft (1.8m) DisplayPort and USB 5Gbps KVM Cable, 4K 60Hz, Universally Compatible DP 1.2/USB 3.0 Combo Cable for KVM Switches

Product ID: DU1226-KVM-CABLE




KVM cable provides a reliable connection between a computer and a DisplayPort KVM switch with USB 5Gbps support.

Simplify cable management by combining multiple connections into a single bundle. This minimizes the number of individual cables that need to be handled, making installation faster and more efficient. They are perfect for environments where KVMs are essential, such as data centers, server rooms, edge networking, and remote management setups, helping to reduce cable clutter and maintain an organized workspace.

This KVM cable works with any operating system, including Windows, macOS, ChromeOS, and Linux. It also supports all major hardware platforms, such as Intel, AMD, and Apple Silicon.

KVM combo cable is DisplayPort 1.2 compliant, supporting resolutions up to 4K at 60Hz, HDR10, and DisplayPort audio for high-quality audio/video experience. The USB 3.0 Type-A to Type-B connector provides fast data transfer speeds of up to 5Gbps.

Certifications, Reports and Compatibility



Applications

- Connect a computer to a DisplayPort KVM Switch with USB 5Gbps host ports

Features

- **KVM COMBO CABLE:** Connect a computer to a Displayport KVM Switch that features USB 5Gbps; It's ideal for desktop workstations and setups where clean cable management and switching between systems are essential; Works with any DP/USB 3.0 KVM
- **OPTIMIZED CABLE MANAGEMENT:** Combines DisplayPort and USB 3.2 Gen 1 in a single bundled cable, reducing setup complexity and streamlining installation for a cleaner, more efficient workspace
- **UNIVERSAL COMPATIBILITY:** Works with any DisplayPort KVM featuring USB 5Gbps; OS independent, supporting all operating systems including Windows, macOS, ChromeOS, and Linux; Compatible with all hardware platforms such as Intel, AMD, and Apple Silicon
- **TECHNICAL SPECIFICATIONS:** KVM Combo Cable is DisplayPort 1.2 compliant, supporting resolutions up to 4K 60Hz, HDR10, and DisplayPort audio; USB 3.0 Type-A to Type-B connector supports up to 5Gbps transfer speeds
- **THE IT PRO'S CHOICE:** Designed for reliability in edge and on-prem deployments, our solutions are lab-tested and field-proven for seamless integration and maximum uptime; Backed by free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers

Performance

Video Revision	DisplayPort 1.2
Maximum Digital Resolutions	4K 60Hz

Connector(s)

Connector A	1 - DisplayPort
	1 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps)
Connector B	1 - DisplayPort
	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

Software

OS Compatibility	No Drivers or Software Required
------------------	---------------------------------

**Physical
Characteristics**

Color	Black
Product Length	6.0 ft [1.8 m]
Product Width	0.8 in [20.5 mm]
Product Height	0.6 in [16 mm]
Weight of Product	5.4 oz [154 g]

**Packaging
Information**

Package Length	5.7 in [14.5 cm]
Package Width	11.4 in [29.0 cm]
Package Height	1.2 in [3.1 cm]
Shipping (Package) Weight	2.9 oz [82.0 g]

What's in the Box

Included in Package	1 - KVM Cable
---------------------	---------------

**Warranty
Information**

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***