

## DVI to Mini DisplayPort Adapter with Audio

**Product ID:** DVI2MDPA



The DVI2MDPA DVI to Mini DisplayPort Adapter (with 2-Channel Audio) converts a DVI-D (Digital), Mini-DVI or HDMI source signal and accompanying audio, for use with a Mini DisplayPort or DisplayPort monitor at resolutions up to 1920x1200.

The adapter offers easy plug-and-play installation with both PC and Mac platforms, ensuring seamless operation with your display to save the time and hassle of hardware upgrades.

A complete, out-of-the-box solution, this DVI-Mini DisplayPort adapter includes all cables necessary for connecting a DVI-D video source and 3.5mm stereo audio to any Mini DisplayPort monitor, including Apple Cinema HD displays, and can also be used with Mini DVI or Mini HDMI sources using additional cables (sold separately - see Accessories).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Use a PC with a DVI or HDMI output with a Mini-DisplayPort monitor
- Convert DVI video and audio to one Mini DisplayPort input on monitors that support audio output
- Adapt a DVI-D output signal and connect supporting audio for use with Apple Cinema Displays

### Features

- Supports resolutions up to 1920x1200

- USB power, 3.5mm audio and Mini-DisplayPort cables included
- Supports stereo audio pass-through to Mini-DisplayPort output (DisplayPort audio support required on monitor)
- Stores and passes EDID information
- USB-powered operation
- No software or drivers required

---

#### Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	DVI-D 3.5 mm Stereo Audio
AV Output	Mini-DisplayPort
Audio	Yes
Industry Standards	Mini-DisplayPort 1.1a DVI 1.0

---

#### Performance

Maximum Digital Resolutions	1920x1200
Wide Screen Supported	Yes

---

#### Connector(s)

Connector A	DVI-D (25 pin) 3.5 mm Mini-Jack (3 Position) USB Mini-B (5 pin)
Connector B	Mini-DisplayPort (20 pin)

---

#### Special Notes / Requirements

Note	Can be used for HDMI input, or standard DisplayPort output using adapters - See Accessories
------	---

---

#### Indicators



LED Indicators                      Power indicator

**Power**

Power Source                      USB-Powered

Input Voltage                      5 DC

**Environmental**

Operating Temperature      0C to 70C (32F to 158F)

Storage Temperature        -10C to 80C (14F to 176F)

Humidity                          10~85% RH

**Physical Characteristics**

Color                                Black

Material                          Aluminum and Plastic

Cable Length                    24.0 in [61 cm]

Product Length                3.3 in [83 mm]

Product Width                 2.4 in [61 mm]

Product Height                0.6 in [14 mm]

Weight of Product             4.1 oz [116 g]

**Packaging Information**

Package Length                8.7 in [22 cm]

Package Width                 7.9 in [20 cm]

Package Height                1.2 in [30 mm]

Shipping (Package) Weight   7.4 oz [210 g]

**What's in the Box**

Included in Package            DVI to Mini-DisplayPort Converter

    3.5mm Stereo Audio cable

    USB mini B male to 2xA male (Split) Cable



Mini DisplayPort cable

User Manual

---

***\*Product appearance and specifications are subject to change without notice.***

