

10 ft DVI to VGA Active Converter Cable – DVI-D to VGA Adapter – 1920x1200

Product ID: DVI2VGAMM10



The DVI2VGAMM10 10ft active DVI to VGA converter cable lets you connect your DVI video source directly to a VGA monitor or projector, with no additional adapters or cables required.

Using precise cable lengths reduces excess cable clutter and ensures a tidy, professional installation with a monitor at your workstation or a projector in your classroom or boardroom.

The DVI2VGAMM10 is 10 feet (3 meters) in length, and part of a complete DVI to VGA adapter cable line, featuring two other cables at 3 feet (DVI2VGAMM3) and 6 feet (DVI2VGAMM6), enabling you to choose a customized cable length for your installation.

Don't be fooled by analog DVI adapters that work with a DVI-I port. They won't work with your digital DVI signal, and won't even fit into a DVI-D port.

The DVI2VGAMM10 is an end-to-end cable adapter solution that connects directly from your digital DVI-D computer to your VGA monitor or projector in one simple cable, saving you the hassle of combining a DVI to VGA adapter with a bulky VGA cable, perfect for connecting a DVI-equipped POS computer or kiosk to a touch screen monitor that only supports VGA.

Plus, unlike most digital DVI to VGA adapters which require a power outlet to convert the video signal, the DVI2VGAMM10 doesn't need external power in most installations. For added convenience and compatibility with low-powered DVI video cards, the DVI2VGAMM10 features an optional integrated USB power source (USB cable not included), making it perfect for boardroom or classroom projectors that require a simple installation, that may need to work with more than one computer system.

In the past converting digital DVI to VGA was a difficult and expensive task that often resulted in upgrading to a DVI-D display. Avoid upgrade costs by connecting your DVI-D video source to your existing VGA display using the DVI2VGAMM10. Plus, because the adapter cable supports video resolution up to 1920x1200 you can rest assured you can use your existing VGA monitor or projector while maintaining high-definition video quality.

The DVI2VGAMM10 is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect a DVI-D computer to your classroom or boardroom projector
- Use in your boardroom or workstation for installations requiring up to 10 feet of cable
- Install in your at home workstation to make your DVI-D computer compatible with your VGA monitor
- Connect a DVI-D cable or satellite set top box to your home theater projector or television
- Connect a DVI-D point-of-sales computer or kiosk to a VGA touch screen

Features

- Reduce clutter and connect your display at greater distances with a long 10ft adapter cable
- Avoid the hassle of additional adapters or cables with a built in cable connecting a digital DVI video source directly to a VGA monitor or projector
- Save upgrade cost by connecting your DVI computer to a VGA monitor or projector
- Supports video resolutions up to 1920x1200
- Active Digital DVI (DVI-D) to VGA conversion
- Adapter and cable in one, with 1x male DVI connector and 1x male VGA connector
- Plug-and-play installation

Prominence

Warranty	3 Years
Description CDW 75 - 1st Line	StarTech.com 10ft DVI to VGA Adapter Cable - Active DVI-D to VGA Converter

Hardware

Active or Passive Adapter	Active
AV Input	DVI-D
AV Output	VGA
Audio	No
Chipset ID	Chrontel - 7101A



Performance

Maximum Cable Length	9.8 ft [3 m]
Maximum Analog Resolutions	1920 x 1200
Maximum Digital Resolutions	PC resolutions up to 1920 x 1200 @ 60 Hz

Connector(s)

Connector Type(s)	USB Micro-B (5 pin)
Connector A	DVI-D (25 pin)
Connector B	VGA (15 pin, High Density D-Sub)

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40%-85%RH

Physical Characteristics

Color	Black
Cable Length	10.0 ft [3.0 m]
Product Length	36.0 in [91.5 cm]
Product Width	1.6 in [40.0 mm]
Product Height	0.6 in [15.0 mm]
Weight of Product	3.2 oz [90.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.7 in [43.0 mm]



Shipping (Package) Weight	6.5 oz [184.5 g]
------------------------------	------------------

**What's in the
Box**

Included in Package	10ft (3m) DVI-D to VGA Converter Cable
---------------------	--

****Product appearance and specifications are subject to change without notice.***

