

## 15ft 4-in-1 USB Dual Link DVI-D KVM Switch Cable w/ Audio & Microphone

Produkt ID: DVID4N1USB15



The DVID4N1USB15 15ft 4-in-1 USB Dual Link DVI-D KVM Switch Cable w/ Audio & Microphone integrates dual link DVI video quality with USB mouse and keyboard, 3.5mm audio out and microphone connections into a single, compact cable.

The four-in-one DVI KVM cable is a cost-effective and convenient solution that's suitable for use with dual link DVI supported USB KVM switches, allowing you to share a USB peripheral set between two computers configured for high definition output.

Backed by a StarTech.com Lifetime Warranty.

<b>Works with:</b>

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS1642, CS1644, CS1784, CS1782, CS1762, CS1764)

Avocent models (2SVDVI10-001, 4SVDVI10-001, SC4UAD, SC420, SC440, SC540)

Belkin models (F1DN102D, F1DN104D, F1DD102L, F1DD104L)

Cables to go models (52047, 52048)

### Certifikat, rapporter och kompatibilitet

### Användning

- Connects a computer to a Dual Link DVI + USB KVM switch with audio and mic support

## Funktioner

- Combines 4 peripheral cables into one
- Dual Link DVI-D signal is supported
- Meets and exceeds all DVI-D and USB 2.0 specifications
- Supports DVI-D Maximum clock frequency in dual link mode up to 7.92 Gbit/s)

---

### Hårdvara

Garantipolicy	Lifetime
Kabelmanteltyp	PVC - Polyvinyl Chloride

---

### Kontakt(er)

Connector A	3.5 mm minijack (3-polig) DVI-D (25-stifts) USB Type-A (4-stifts) USB 2.0
Connector B	3.5 mm minijack (3-polig) DVI-D (25-stifts) USB B (4-stifts)

---

### Utseende

Färg	Svart
Kabellängd	15.0 ft [4.6 m]
Produktlängd	15.0 ft [4.6 m]
Produktbredd	1.6 in [39.5 mm]
Produkt höjd	0.6 in [15.5 mm]
Produktvikt	31.2 oz [885 g]

---

### Förpackning

Package Length	12.8 in [32.5 cm]
----------------	-------------------



Package Width	9.8 in [25 cm]
Package Height	2.8 in [70 mm]
Fraktvikt (förpackning)	31.2 oz [885 g]

---

Vad det är i lådan

Ingår i paketet	4-n-1 DVI-D USB KVM Cable
-----------------	---------------------------

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

