

2 Port ExpressCard Laptop 1394a FireWire Adapter Card

Product ID: EC13942



This 2 Port ExpressCard Laptop 1394a Firewire Adapter Card provides a stable platform for virtually any FireWire 400 device connection.

Ensuring seamless operation with peripherals connected through FireWire 400, the ExpressCard 1394a FireWire Adapter supports data transfer rates at up to 400Mbps - perfect for connecting FireWire-capable multimedia devices, editing multimedia content or simply transferring large volumes of data from a computer to FireWire-connected external storage.

Certifications, Reports and Compatibility



Applications

- Add a high speed FireWire port to a laptop without any FireWire ports
- Connect a digital camera to a laptop with an ExpressCard slot to download photos or video
- Connect a high speed external hard drive to an ExpressCard enabled system

Features

- Two 6-pin FireWire ports, each with transfer rates up to 400 Mbps
- Compliant with IEEE 1394-1995, 1394a-2000 and OHCI 1.1 standards
- Fits in 34mm and 54mm ExpressCard slots
- Plug-and-Play and hot-swap compatible

Hardware

Warranty

Lifetime

Ports	2
Interface	FireWire 400 (1394a)
Bus Type	ExpressCard
Card Type	34mm ExpressCard
Chipset ID	Texas Instruments - XIO2200A

Performance	Maximum Data Transfer Rate	400 Mbps
--------------------	----------------------------	----------

Connector(s)	Connector Type(s)	ExpressCard (34mm)
	External Ports	FireWire 400 (6 pin, IEEE 1394a)

Software	OS Compatibility	Windows 2000, XP, Vista, 7, 8 Windows Server 2003, 2008 R2, 2012, 2016 Linux 3.5.x to 4.4.x <i>LTS Versions only</i>
-----------------	------------------	--

Special Notes / Requirements	System and Cable Requirements	One available ExpressCard Slot
-------------------------------------	-------------------------------	--------------------------------

Power	Power Source	Not Included (not required for standard applications)
	Output Voltage	12V DC
	Output Current	1A+
	Center Tip Polarity	Positive
	Plug Type	H

Physical Characteristics	Product Length	4.7 in [1.2 cm]
	Product Width	1.3 in [34.000 mm]
	Product Height	0.7 in [19.000 mm]
	Weight of Product	3.5 oz [100.000 g]

Packaging Information	Package Length	5.9 in [1.5 cm]
	Package Width	3.0 in [76.000 mm]
	Package Height	9.6 in [2.4 cm]
	Shipping (Package) Weight	5.1 oz [144.000 g]

What's in the	Included in Package	FireWire ExpressCard
----------------------	---------------------	----------------------

Box

Included in Package	4-6 Pin FireWire Cable
Included in Package	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

