

2 Port ExpressCard eSATA Controller Adapter Card

Produkt ID: ECESATA22



This 2 Port eSATA ExpressCard adapter lets laptop users experience the high performance capability of eSATA storage for data transfer rates of up to 3Gbps, as well as port multiplier capability with command-based switching for connecting multiple external hard drives to a host PC or Mac notebook through one eSATA connection.

Using a native PCI Express single chipset, the eSATA controller provides enhanced compatibility, reliability and performance for your external storage needs.

Certifikat, rapporter och kompatibilitet



Användning

- Add eSATA connectivity to a laptop to connect with high speed external storage devices
- Upgrade from connecting external storage devices with USB 2.0 to faster eSATA

Funktioner

- Two external SATA (eSATA) ports
- Supports FIS and Command-based Port Multiplier technology
- Fits in 34mm and 54mm ExpressCard slots
- Compliant with Serial ATA 2.5 specifications with transfer rates up to 3.0 Gbps
- Hot-Swap compatible
- Uses native PCI Express single chipset

Hårdvara

Garantipolicy	Lifetime
Portar	2
Gränssnitt	eSATA
Busstyp	ExpressCard
Korttyp	ExpressCard 34mm
Chipset-ID	Silicon Image - SiI3132

Prestanda

Typ och hastighet	SATA 3 Gbit/s (SATA II)
Port Multiplier	Ja
RAID	Nej

Kontakt(er)

Kontakttyp(er)	1 - ExpressCard (34mm)
Externa portar	2 - eSATA (7-stifts, data)

Mjukvara

OS-kompatibilitet	Windows® 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server® 2003, 2008 R2, 2012 Mac OS X® 10.6 to 10.11 Linux 3.5.x to 4.4.x LTS Versions only
-------------------	---

Utseende

Produktlängd	4.4 in [11.2 cm]
Produktbredd	1.3 in [3.4 cm]
Produkthöjd	0.8 in [2.1 cm]
Produktvikt	1.4 oz [40 g]

Förpackning

Paketets längd	6.8 in [17.2 cm]
Paketets bredd	2.8 in [72 mm]
Paketets höjd	7.3 in [18.5 cm]
Fraktvikt (förpackning)	0.2 lb [0.1 kg]

Vad det är i lådan

Ingår i paketet	1 - eSATA ExpressCard Controller Card
	1 - Driver CD
	1 - Instruction Manual

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.