

## 4 Port ExpressCard Laptop USB 2.0 Adapter Card

Productcode: EC400USB



This 4 Port ExpressCard USB 2.0 Adapter Card adds four USB 2.0 compliant ports to a host computer using an available ExpressCard slot, and is backward compatible with the USB 1.1 specification, for use with older USB peripherals.

The ExpressCard adapter can be installed in seconds, and offers combined hi-speed USB 2.0 data transfer rates of up to 480Mbps - ensuring a reliable and efficient connection with MP3 players, digital cameras, external CD/DVD-ROM drives, or virtually any USB device you need to connect to your laptop computer.

Designed to provide reliable USB connections, this ExpressCard adapter is backed by StarTech.com's lifetime warranty and free lifetime technical support.

## Certificaties, rapporten en compatibiliteit

### Toepassingen

- Digital cameras
- DVD drives
- External CDR/RWs
- Flash card readers/writers
- iPod connectivity

- Joysticks
- Mice and keyboards
- MP3 players
- PDAs
- Portable hard drives
- Printers
- Scanners
- Webcams

## Eigenschappen

- Backward compatible with USB version 1.1
- Connect up to 127 devices by cascading multiple hubs
- Combined Data transfer rate of up to 480 Mbps
- Easy plug-and-play installation
- Provides up to 500 mA of power per port

---

### Hardware

Garantiebeleid	Lifetime
Poorten	4
Interface	USB 2.0
Bus type	ExpressCard
Kaarttype	34mm ExpressCard
Chipsetcode	Genesys Logic - GL850A


---

### Prestaties

Maximale overdrachtsnelheid	480 Mbps
-----------------------------	----------

---

### Connector(en)



Type connector(en)	ExpressCard (34mm)
Externe poorten	USB Type-A (4-polig) USB 2.0

---

#### Software

Besturingssystemen	Windows® 10 (32/64), 8 / 8.1 (32/64), 7 (32/64), Vista (32/64), XP (32/64)  Windows Server® 2012, 2008 R2, 2003  Mac OS® 10.x (tested up to 10.11)  Linux 2.6 and later (tested up to 3.5)
--------------------	--

---

#### Voeding

Inclusief voedingsadapter	Niet meegeleverd (niet vereist voor standaardapplicaties)
Ingangsspanning	115V AC
Uitgangsspanning	5 DC
Uitgangsstroom	2.6A
Polariteit pin midden	Positief
Stekkertype	H

---

#### Fysieke eigenschappen

Lengte product	4.5 in [11.5 cm]
Breedte product	1.3 in [34 mm]
Hoogte product	0.8 in [21 mm]
Gewicht product	7.8 oz [220 g]

---

#### Verpakkingsinformatie

Package Length	8.1 in [20.7 cm]
Package Width	5.5 in [14 cm]
Package Height	1.5 in [38 mm]
Verzendgewicht (verpakt)	4.2 oz [120 g]



---

Wat wordt er  
meegeleverd

Meegeleverd

4 Port ExpressCard USB 2.0 Hub

Instruction Manual

---

\* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

