

## 2 Port ExpressCard 54mm eSATA II Controller Adapter Card

Produkt ID: ECESATA254



This 2 port eSATA Controller ExpressCard (54mm) Adapter offers provides two eSATA ports, allowing you to connect eSATA external SATA storage to your laptop computer through an ExpressCard port.

The ExpressCard eSATA controller features port multiplier support with FIS-based switching, allowing multiple eSATA hard drives to be accessed using a single eSATA port. Plus, the adapter card uses a native PCI Express (single) chipset that provides enhanced compatibility, reliability and performance for external storage applications, with support for high speed eSATA data transfer rates of up to 3Gbps.

### Certifikat, rapporter och kompatibilitet

#### Användning

- Connects devices using eSATA standard connection to your notebook
- With a quicker maximum data transfer rate (3 Gbps), it makes it easier to do data off loads

#### Funktioner

- Compliant with Serial ATA 1.0 specifications and ExpressCard 54mm Form Factor
- Supports Native Command Queuing (NCQ) hard drives
- Hot-Swapping capabilities

- Compatible with PCI Express 1-lane (x1)
- Works with SATA I/II devices with transfer speeds up to 3.0 Gbps
- Compliant with ExpressCard/54mm standard
- Native single chipset design for maximum compatibility and performance
- Port Multiplier support

---

#### Hårdvara

Garantipolicy	Lifetime
Portar	2
Gränssnitt	eSATA
Busstyp	ExpressCard
Korttyp	ExpressCard 54mm
Chipset-ID	Silicon Image - SiI3132

---

#### Prestanda

Maximal dataöverföringshastighet	3 Gbps
Typ och hastighet	SATA 3 Gbit/s (SATA II)
Port Multiplier	Ja
RAID	Nej

---

#### Kontakt(er)

Kontakttyp(er)	ExpressCard (54mm)
Externa portar	eSATA (7-stifts, data)

---

#### Mjukvara

OS-kompatibilitet	Windows® 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server® 2003, 2008 R2, 2012 Mac OS X® 10.6 to 10.11 Linux 3.5.x to 4.4.x <i>LTS Versions only</i>
-------------------	--

---

Särskilda  
anmärkningar/krav

System- och kabelkrav Notebook with an ExpressCard 54mm slot

---

Utseende

Produktlängd	4.4 in [11.3 cm]
Produktbredd	2.3 in [59.5 mm]
Produkthöjd	0.6 in [16 mm]
Produktvikt	1.4 oz [40 g]

---

Förpackning

Package Length	7.2 in [18.2 cm]
Package Width	6.7 in [17 cm]
Package Height	2.5 in [64 mm]
Fraktvikt (förpackning)	3.9 oz [110 g]

---

Vad det är i lådan

Ingår i paketet	eSATA ExpressCard
	Driver CD
	Instruction Manual

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

