

## 20-Slot 2U Rack Mount Media Converter Chassis for ET Series 2 Fiber Media Converter

**Product ID:** ETCHS2U



The ETCHS2U 20-Slot 2U Rack Mount Media Converter Chassis for ET Series 2 Media Converters lets you add an un-managed, 20-slot media converter chassis to your rack or cabinet to provide central power and cooling.

The media converter rack includes a single 200W power supply to centrally power all 20 slots, with an additional slot to add a redundant power supply (ETCHS2UPSU) for maximum up-time. It also includes two cooling fans (one per side) to help extend the life of your media converters.

A perfect accessory to the StarTech.com ET series 2 converters, the 2U chassis is designed so that all critical components (Power, Fans and Media Converter Cards) are hot swappable to avoid network disruption.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Centrally mount and power up to 20 media converter units with a single chassis, while providing additional cooling and optional redundant power

### Features

- 2U 20-slot Media Converter Chassis with AC/DC power
- All modules and cards support hot-swapping
- 2 removable cooling fans included

- Single 200W Power Supply included - [redundant power supply](/product/ETCHS2UPSU) (ETCHS2UPSU) also available - sold separately

---

#### Hardware

Warranty	2 Years
Frame Type	Open Frame
U Height	2U
Fan(s)	Yes
Fans	80 mm
Mounting Options	Front Mount (Front Only)

---

#### Performance

Air Flow Rate	59.37 CFM
Noise Level	44.5 dBA
MTBF	65,000 Hours (25C)

---

#### Power

Power Source	Standard 120V Power Cords
Input Voltage	110V-240V AC
Input Current	2.2 A
Output Voltage	12V DC
Output Current	16.6 A
Power Consumption (In Watts)	60

---

#### Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	5~90% RH Non-condensing

---

#### Physical Characteristics

Color	Black
-------	-------



Material	Steel
Rail Thickness	0.0 in [1 mm]
Product Length	15.5 in [39.4 cm]
Product Width	20.4 in [51.7 cm]
Product Height	6.5 in [16.4 cm]
Weight of Product	13.4 lb [6.1 kg]

---

**Packaging Information**

Package Length	22.3 in [56.7 cm]
Package Width	17.2 in [43.8 cm]
Package Height	7.5 in [19.1 cm]
Shipping (Package) Weight	18.5 lb [8.4 kg]

---

**What's in the Box**

Included in Package	2U Media Converter Chassis
	Power Cords (NA/EU/UK)
	Instruction Manual
	Grounding Screw

---

***\*Product appearance and specifications are subject to change without notice.***

