

## 14-in-1 USB 2.0 High Capacity Silver Multi Media Memory Card Reader

**Product ID:** FCREADHC



This USB 2.0 14-in-1 Media Memory Card Reader offers fast and convenient access to the most popular media/memory card formats including SD, Compact Flash, MMC, Memory Stick and IBM Micro Drive as well as SDHC cards for applications requiring high capacity storage.

Simply connect the card reader to a USB 2.0 port on the host computer, then insert the memory card into the reader for read/write access to the contents of the media/memory card. The card reader supports full hi-speed transfer rates of up to 480Mbps using a USB 2.0 connection and is backward compatible with USB 1.1, ensuring compatibility with virtually any USB capable computer.

### Certifications, Reports and Compatibility

### Applications

- Mobile users/travelers who need a compact and lightweight yet full featured card reader
- Transfer photos from a digital camera memory card to a laptop or desktop
- Transfer music from a computer to a memory card for use in a portable music player

### Features

- Support for CompactFlash (CF type I/II, MicroDrive), SmartMedia (SM, SM RAM), MultiMedia Card (MMC, RS MMC), SecureDigital (SD, Micro SD, SDHC) and MemoryStick (MS, MS Pro, MS Duo, MS Pro Duo, MS MG)
- Powered directly from the USB port
- Compact and lightweight design

- High Speed USB 2.0 host interface with support for transfer rates up to 480 Mbps
- Plug-and-Play and Hot-Swap compatible

---

**Performance**

|                            |  |
|----------------------------|--|
| Warranty                   | 2 Years  |
| Maximum Data Transfer Rate | 480 Mbps   |
| Memory Media Type          | CF (Compact Flash I/II Card)<br>IBM Micro Drive<br>SM (SmartMedia)<br>SD/MMC (Secure Digital/Multimedia Card)<br>RS-MMC (Reduced Size Multimedia Card)<br>SDHC (Secure Digital High Capacity)<br>MS/MS Pro (Memory Stick/Memory Stick Pro)<br>MS Duo, MS Pro Duo, MS Pro-HG Duo<br>Mini-SD, Micro-SD (Mini/Micro Secure Digital) |

---

**Connector(s)**

|                   |   |
|-------------------|---|
| Connector Type(s) | USB Type-A (4 pin) USB 2.0  |
| External Ports    | CompactFlash (50 pin) Slot<br>Memory Stick / Memory Stick Pro Slot<br>Memory Stick Duo / Memory Stick Pro Duo Slot<br>MiniSD / MicroSD / MMC Slot<br>SD / MMC Slot<br>SmartMedia Slot<br>USB Mini-B (5 pin) |

---

**Physical Characteristics**

|          |         |
|----------|---------|
| Material | Plastic |
|----------|---------|



|                   |                |
|-------------------|----------------|
| Product Length    | 2.3 in [59 mm] |
| Product Width     | 2.3 in [59 mm] |
| Product Height    | 0.6 in [15 mm] |
| Weight of Product | 1.5 oz [42 g]  |

---

**Packaging Information**

|                           |                  |
|---------------------------|------------------|
| Package Length            | 5.4 in [13.8 cm] |
| Package Width             | 1.6 in [40 mm]   |
| Package Height            | 7.2 in [18.2 cm] |
| Shipping (Package) Weight | 6.0 oz [170 g]   |

---

**What's in the Box**

|                     |                                  |
|---------------------|----------------------------------|
| Included in Package | Card Reader                      |
|                     | 3 ft. USB Mini B to Type A cable |
|                     | Instruction Manual               |

---

***\*Product appearance and specifications are subject to change without notice.***

