

USB Multi Media Memory Card Reader Adapter

Produkt ID: FCREADMICRO



An ideal laptop or desktop accessory, this pocket-sized memory card reader connects to a computer through USB to support the most popular memory card formats, providing an all-in-one flash memory solution.

This multi-format Memory Card Reader supports Memory Stick, MS Pro, MS Duo, MS Pro Duo, MS MG, MS Micro (M2), Micro SD, Mini SD, RS MMC/MMC 4.0, Ultra II SD, Extreme SD, Extreme II SD, T-Flash (No Adapter Required) and more, as well as high capacity cards such as SDHC and SDXC. Plus, this card reader is backward compatible with older card formats such as SD, to ensure you can access and write to your memory card without any hassles.

Certifikat, rapporter och kompatibilitet

Användning

- Mobile users/travelers who need a compact and lightweight card reader small enough to fit in a pocket
- Transfer photos from a digital camera memory card to a laptop or desktop
- Transfer music from a computer to a memory card for use in a portable music player

Funktioner

- Support for MultiMedia Card (MMC, RS MMC), Secure Digital (SD, Micro SD, Mini SD, SDHC, SDXC) and Memory Stick (MS, MSPro, MS Duo, MSProDuo, M2, MS MG)

- Powered directly from the USB port
- Ultra compact and lightweight design
- High Speed USB 2.0 host interface with support for transfer rates up to 480 Mbps
- Plug-and-Play and Hot-Swap compatible

Prestanda

Garantipolicy	2 Years
Maximal dataöverföringshastighet	480 Mbps
Minnesmediatyp	RS-MMC (Reduced Size Multimedia Card) SD/MMC (Secure Digital/Multimedia Card) Mini-SD, Micro-SD (Mini/Micro Secure Digital) SDHC (Secure Digital High Capacity) microSDHC (Micro Secure Digital High Capacity) MS/MS Pro (Memory Stick/Memory Stick Pro) M2 (Memory Stick Micro) MS Duo, MS Pro Duo, MS Pro-HG Duo MS MG (Memory Stick med MagicGate) SDXC (Secure Digital eXtended Capacity)

Kontakt(er)

Externa portar	Memory Stick/Memory Stick Pro-plats Memory Stick Duo-/Memory Stick Pro Duo-plats Memory Stick Micro-plats (M2) MiniSD / MicroSD / MMC Slot SD-/MMC-plats
----------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------



USB Type-A (4-stifts) USB 2.0

Mjukvara

OS-kompatibilitet	Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and Mac OS 9 and above
-------------------	------------------------------------------------------------------------------------------------------------------------------------------

Utseende

Färg	Svart
Kabinetttyp	Av plast
Produktlängd	3.7 in [93 mm]
Produktbredd	0.8 in [20 mm]
Produkt höjd	0.4 in [10 mm]
Produktvikt	0.6 oz [17 g]

Förpackning

Förpackningsantal	1
Package Length	4.5 in [11.4 cm]
Package Width	0.7 in [18 mm]
Package Height	6.0 in [15.3 cm]
Fraktvikt (förpackning)	1.4 oz [40 g]

Vad det är i lådan

Ingår i paketet	USB Card Reader
	Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

