

## USB 3.0 Multi Media Flash Memory Card Reader

Product ID: FCREADHCU3



The FCREADHCU3 USB 3.0 Card Reader enables easy read/write access to a variety of popular flash memory card formats/types (CompactFlash, Secure Digital, Memory Stick) in a single unit, over a high speed USB 3.0 connection.

Using a connection over USB 3.0, which is up to 10 times faster than the USB 2.0 standard, makes transferring large data files much quicker; it (USB 3.0) is still backward compatible with USB 2.0 however, ensuring compatibility with older systems.

This compact and lightweight external card reader offers a portable, convenient solution for accessing many different types of Flash Memory/Media cards and is easy to use, with no driver or software installation required.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Laptop users looking to be able to access one or more types of flash memory cards
- Professionals looking to access their high speed flash memory cards over USB 3.0, instead of USB 2.0

### Features

- SuperSpeed USB 3.0 host interface standard, which supports transfer rates up to 5 Gbps
- Compatible with various types of CompactFlash, SecureDigital and MemoryStick flash cards
- Backward compatible with USB 2.0 computer systems
- Power indicator LED

- No driver or software installation required
- Compact design and lightweight plastic construction
- Powered directly from the USB port

<b>Hardware</b>	Warranty	2 Years
	Interface	USB 3.0
	Chipset ID	Genesys Logic - GL3220
<b>Performance</b>	Memory Media Type	MS Duo, MS Pro Duo, MS Pro-HG Duo
	Memory Media Type	CF (Compact Flash I Card)
	Memory Media Type	SDXC (Secure Digital eXtended Capacity)
	Memory Media Type	SDHC (Secure Digital High Capacity)
	Memory Media Type	microSDHC (Micro Secure Digital High Capacity)
	Memory Media Type	SD/MMC (Secure Digital/Multimedia Card)
	Memory Media Type	M2 (Memory Stick Micro)
	Memory Media Type	MS MG (Memory Stick w/ MagicGate)
	Memory Media Type	MS/MS Pro (Memory Stick/Memory Stick Pro)
	Memory Media Type	RS-MMC (Reduced Size Multimedia Card)
	Memory Media Type	MSXC (Memory Stick eXtended Capacity)
	Memory Media Type	Mini-SD, Micro-SD (Mini/Micro Secure Digital)
<b>Connector(s)</b>	Connector Type(s)	USB Type-B (9 pin) USB 3.0
	External Ports	SD / MMC Slot
	External Ports	CompactFlash (50 pin) Slot
	External Ports	MiniSD / MicroSD / MMC Slot
	External Ports	Memory Stick / Memory Stick Pro Slot
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Special Notes / Requirements</b>	System and Cable Requirements	Available USB port
<b>Indicators</b>	LED Indicators	Power
<b>Power</b>	Power Source	USB-Powered
	Input Voltage	100 - 240 AC

Input Current	0.8 A
Output Voltage	5 DC
Output Current	4 A
Power Consumption (In Watts)	20

---

<b>Environmental</b>	Operating Temperature	-40C to 80C (-40F to 176F)
	Storage Temperature	-65C to 150C (-85F to 302F)
	Humidity	5% ~ 90% RH

---

<b>Physical Characteristics</b>	Color	Black
	Material	Plastic
	Product Length	3.3 in [85.000 mm]
	Product Width	2.2 in [55.000 mm]
	Product Height	0.8 in [20.000 mm]
	Weight of Product	1.9 oz [54.000 g]

---

<b>Packaging Information</b>	Package Quantity	1
	Package Length	6.8 in [1.7 cm]
	Package Width	5.6 in [1.4 cm]
	Package Height	1.3 in [32.000 mm]
	Shipping (Package) Weight	6.0 oz [169.000 g]

---

<b>What's in the Box</b>	Included in Package	USB 3.0 Card Reader
	Included in Package	USB 3.0 Cable
	Included in Package	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

