


3m Fiber Optic Cable - Multimode Duplex 62.5/125 LSZH Fiber Jumper Cord - LC/ST

Produkt ID: FIBLCST3



The FIBLCST3 3-meter (10ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated with one LC (male) connector and one ST (male) connector, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This LC-ST patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our LC-ST Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

Certifikat, rapporter och kompatibilitet



Användning

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems

- Telecommunication/Data communication
- Used by long distance networks with mission critical data

Funktioner

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

Hårdvara

Garantipolicy	Lifetime
Fiberstorlek	62.5/125
Brandteknisk klass	LSZH-klassad (Low Smoke Zero Halogen)
Fiberklassificering	OM1

Prestanda

Maximal dataöverföringshastighet	10Gbps
Kabelklassificering	1Gbps / 10Gbps
Fibertyp	Multiläge

Kontakt(er)

Connector A	1 - Fiberoptisk LC duplex
Connector B	1 - Fiberoptisk ST duplex

Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	0~90% RH

Utseende

Färg	Orange
Kabellängd	9.8 ft [3 m]
Produktlängd	9.8 ft [3.0 m]
Produktbredd	0.5 in [1.2 cm]
Produkthöjd	0.3 in [0.7 cm]
Produktvikt	1.8 oz [52.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	6.9 in [17.4 cm]
Paketets bredd	6.6 in [16.8 cm]
Paketets höjd	1.2 in [3.0 cm]
Fraktvikt (förpackning)	2.2 oz [62.0 g]

Vad det är i lådan

Ingår i paketet	1 - 3m Multimode 62.5/125 Duplex Fiber Patch Cable LC - ST
-----------------	--

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.