


No-Stud TV Wall Mount - Low Profile Heavy Duty VESA TV Wall Mount for up to 80 inch Display (110lb/50kg) - Universal Television Wall Mount - Studless Tilting Flat Screen Mount

Product ID: FPWHANGER



This No-Stud TV Wall Mount enables you to easily and securely mount your display from 37" up to 80" to walls without the need to align the bracket with wall studs. Its steel frame supports displays up to 110lb / 50kg in weight and provides the ability to tilt your display to ensure your application and the ideal viewing angle are aligned.

The studless design of this Universal TV Wall Mount makes it easy for you to mount your TV to a drywall or plaster wall in any boardroom, office, or classroom setup. Simply choose the best mounting location and secure the mounting bracket into the wall (with included nails); no need to drill, look for wall studs, and useful for offices and environments with metal studs. The included Automatic Spring Lock lets you conveniently mount and secure your TV in place.

This Low Profile TV Wall Mount is perfect for applications like digital signage, where space and aesthetics are important. With a 1.2" profile from the wall, this Wall Mount TV Hanger provides a professional and clean look.

The Hanging TV Wall Mount lets you angle your TV towards your audience. The included wall-mounted spacers give you a choice to change the tilting angle (0/ -5) for a comfortable viewing experience.

The FPWHANGER is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Safely and securely wall-mount your TV to studless walls
- Ideal for lobbies, education environments and meeting spaces

- Create a professional looking digital signage setup

Features

- **LARGE 80" NO-STUD TV WALL MOUNT:** Low profile TV wall mount supports VESA compatible displays incl. curved TVs up to 80 inch (110 lb/50 kg) w/ support for many VESA patterns; Ideal for unusual stud placement or anywhere on a wall in between studs
- **EASY INSTALLATION:** Mount your TV without studs on drywall; The steel frame guides 20 nails into the wall on an angle to increase the load bearing strength; The picture hanger style simplifies the final step of mounting the TV
- **SLIM DESIGN:** Studless TV wall mount with a minimal profile of only 1.2" (3cm) is provided with large wall-mounted spacers to give you a choice for the tilting angle (0/-5)
- **SECURE MOUNTING:** Heavy duty TV wall mount with Automatic Spring Locks and a convenient Quick Release Cord to prevent the flat screen/panel from being easily removed; Ideal for hanging TV on drywall/plaster walls, no drill required
- **COMPATIBILITY:** Universal LCD/LED television mount supports LG, Samsung, Sony, Sharp, others (screws/spacers incl) & VESA bracket hole patterns 100x200, 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400

Hardware

Warranty	5 Years
Wallmountable	Yes
# of Displays Supported	1
Mounting Options	Wall-Mount
Minimum Profile from Wall	1.2 in [31 mm]
VESA Hole Pattern(s)	100x200 mm
	200x200 mm
	200x300 mm
	200x400 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm

400x400 mm

600X200 mm

600x300 mm

600x400 mm

Performance

Weight Capacity (Per Display)	110.2 lb [50 kg]
Minimum Display Size	37"
Maximum Display Size	80"
Fits Curved Display	Yes
Video Wall	No
Display Tilt	0 / -5
Anti-theft	No

Physical Characteristics

Color	Black
Material	Steel
Internal Width	27.6 in [70 cm]
Internal Height	5.2 in [13.3 cm]
Internal Depth	1.2 in [3.1 cm]
Product Length	5.2 in [13.3 cm]
Product Width	27.6 in [70.0 cm]
Product Height	1.2 in [3.1 cm]
Weight of Product	5.4 lb [2.4 kg]

Packaging Information

Package Quantity	1
Package Length	30.6 in [77.7 cm]

Package Width	7.9 in [20.0 cm]
Package Height	2.0 in [5.2 cm]
Shipping (Package) Weight	5.6 lb [2.5 kg]

What's in the Box

Included in Package	1 - Wall mount assy.
	1 - Display mounting bracket
	2 - Tilt spacers, large
	2 - Tilt spacers, small
	4 - M5 x 14 screws
	4 - M6 x 14 screws
	4 - M6 x 30 screws
	4 - M8 x 30 screws
	4 - M8 x 50 screws
	4 - Washers, small
	4 - Washers, medium
	8 - Mounting spacers, short
	8 - Mounting spacers, long
	4 - Mounting screws
	4 - Concrete anchors
	4 - Washers, large
	20 - Nails

****Product appearance and specifications are subject to change without notice.***