

TV Wall Mount supports up to 70 inch VESA Displays - Low Profile Full Motion Universal TV Flat Screen Wall Mount - Heavy Duty Adjustable Tilt/Swivel Articulating Arm Bracket

Product ID: FPWARTB2



Maximize space while creating an impressive display. This full-motion TV wall mount supports flat-screen TVs from 32" to 70" in size, with a weight capacity of 99 lb. (45 kg).

Mount your flat-screen TV in a location that's convenient for visitors, clients and employees, and free up valuable space. The wall mount is ideal for a lobby, boardroom or other venue. The TV wall mount also includes built-in cable management to keep cables neatly out of sight.

The TV wall mount features dual arms that extend out to 20.4" (517 mm) from the wall to provide a wide range of movement and accommodate different screen positions and angles. The arms can also fold to tuck in closely to the wall, providing a low profile that enables your display to be positioned just 2.24" (57 mm) from the wall.

You can swivel your display +90 / -90 degrees and tilt +5 / -8 degrees, letting you angle your TV display toward your audience. Plus, the tilt feature lets you adjust the TV so that you can view it comfortably at any height. A built-in level adjustment also offers 5 degree clockwise and counterclockwise turning, to ensure your display is perfectly level.

The heavy-duty steel construction, dual-arm design and dual-stud mounting for studs placed 16" apart, provides increased durability and security. It safely and securely supports your flat-screen TV, to protect your investment.

FPWARTB2 is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Wall-mount your flat-screen TV for optimal viewing
- Ideal for lobbies, boardrooms, meeting spaces and classrooms
- Keep your guests informed and entertained

Features

- **LARGE 70" TV WALL MOUNT:** This heavy-duty TV wall mount supports VESA compatible displays (incl. curved TVs) up to 70 inch (99 lb/45 kg) w/ a durable full-motion steel frame and a powder-coated finish
- **WIDE RANGE OF MOTION:** Articulating & adjustable TV wall mount offers +/-90 swivel, +2/-15 tilt & +/-5 LCD screen level adjustment without the use of additional tools to ensure display is level
- **EXTENDING ARMS:** Arms extend from 2.4" (57mm) to 20.4" (517mm) from the wall; With the length of the arms, center of the television display has an overall lateral range (left to right) of 34.6" (880mm)
- **COMPATIBILITY:** Universal TV wall mount supports LG, Samsung, Sony, Sharp, and others (screws/spacers incl) & VESA hole patterns 200x200, 400x200, 300x300, 400x400, 600x400, 400x300, 300x200.
- **TIDY AESTHETIC:** The flat panel TV wall mounting bracket w/ integrated cable management & optional black snap-on covers keeps cables organized; ideal for customer-facing digital signage

Hardware	Warranty	5 Years
	Wallmountable	Yes
	Cable Management	Yes
	Articulating	Yes
	# of Displays Supported	1
	Mounting Options	Wall-Mount
	Minimum Profile from Wall	2.2 in [57 mm]
	VESA Hole Pattern(s)	200x200 mm
	VESA Hole Pattern(s)	400x200 mm
	VESA Hole Pattern(s)	300x300 mm
	VESA Hole Pattern(s)	400x400 mm
	VESA Hole Pattern(s)	600x400 mm
	VESA Hole Pattern(s)	400x300 mm
	VESA Hole Pattern(s)	300x200 mm
Performance	Weight Capacity (Per Display)	99.4 lb [45 kg]
	Minimum Display Size	32"
	Maximum Display Size	70"
	Fits Curved Display	Yes
	Video Wall	No
		20.4 in [5.2 cm]

Maximum Arm Extension	+5 / -8
Display Tilt	+90 / -90
Swivel / Pivot	No
Anti-theft	

Physical Characteristics	Color	Black
	Material	Steel and Plastic
	Product Length	25.3 in [6.4 cm]
	Product Width	20.4 in [5.2 cm]
	Product Height	16.5 in [4.2 cm]
	Weight of Product	14.9 lb [6.8 kg]

Packaging Information	Package Length	16.3 in [4.2 cm]
	Package Width	24.5 in [6.2 cm]
	Package Height	3.5 in [90 mm]
	Shipping (Package) Weight	17.1 lb [7.7 kg]

What's in the Box	Included in Package	wall mount
	Included in Package	vertical brackets
	Included in Package	horizontal brackets
	Included in Package	wrench
	Included in Package	bracket screws
	Included in Package	nuts
	Included in Package	mounting screws
	Included in Package	M5x14 mm screws
	Included in Package	M6x14 mm screws
	Included in Package	M6x30 mm screws
	Included in Package	M8x30 mm screws
	Included in Package	M8x50 mm screws
	Included in Package	small washers
	Included in Package	large washers
	Included in Package	small spacers

Included in Package	large spacers
Included in Package	screws
Included in Package	concrete screws
Included in Package	bracket washers
Included in Package	instruction manual

****Product appearance and specifications are subject to change without notice.***

