

4 Port USB 3.0 Hub - USB-A to 4x USB-A - SuperSpeed 5Gbps Portable USB 3.1 Gen 1 Type-A Hub - USB Bus Powered - Laptop/Desktop USB Hub with Long Cable 28cm & Cable Management

**Product ID:** HB30AM4AB



This 4 Port USB Hub enables you to connect four SuperSpeed USB 3.2 Gen 1 (5 Gbps) peripherals to your USB-A laptop or computer, an ideal solution for adding USB ports to a device that has limited USB ports available. It features a wrap-around cable manager, allowing you to tuck away the built-in cable for easy portability.

Note: USB 3.2 Gen 1 (5 Gbps) is also known as USB 3.1 Gen 1 (5 Gbps), and USB 3.0 (5 Gbps).

With this USB hub you can connect four USB-A devices to a single USB-A port on your host device. The USB Type-A hub shares up to 4.5W (5V/900mA) of power between connected devices, making it an ideal solution for connecting SSD/thumb drives, data storage, keyboards, mice, web cams and USB headsets. The USB hub is backward compatible with USB 2.0 (480 Mbps).

Featuring a durable plastic housing that's lightweight, and a sleek wrap-around cable management system, this USB hub is the perfect travel companion for your laptop. Its small footprint ensures it will store easily in your laptop bag, and the wrap-around cable manager prevents tangles, ensuring easy accessibility. The USB hub is bus powered so there's no bulky external power adapter.

The USB hub is OS independent ensuring support on a wide range of platforms including Windows, macOS, Linux, iPadOS, Chrome OS and Android. The built-in host cable is 11 in. (28 cm) long, providing enough length to easily integrate into any workstation, reaching your host device even when it's placed on a laptop riser or stand. The USB-A host connection works with any USB Type-A laptop, or 2-in-1, such as Surface Pro 7, Surface Book, MacBook, XPS or X1 Carbon.

HB30AM4AB is backed by a StarTech.com 2-year warranty and free lifetime 24/5 multi-lingual North American based technical support. StarTech.com has been the IT professionals' choice for over 30 years.

## Certifications, Reports and Compatibility

## Applications

- Connect SSD/thumb drives, data storage devices, keyboards, mice, web cams and USB headsets to your USB-A computer
- Store in your laptop bag while traveling

## Features

- **4-PORT USB 3.0 HUB:** Expand the connectivity of a USB-A laptop or desktop PC by adding 4x USB-A ports with this USB 3.2/3.1 Gen 1 SuperSpeed 5Gbps hub; Supports USB 3.0/2.0 devices
- **ORGANIZED & PORTABLE:** Compact USB-A hub with hideaway cable management to prevent tangles in laptop bags or pockets; Lightweight travel hub w/ durable plastic housing, 11" (28 cm) attached USB-A cable ideal for use at the office or home office
- **BUS POWERED USB HUB:** USB Type-A hub w/ speeds up to 5Gbps & shared power up to 4.5W, dependent on power provided by your computer; Supports SSD/thumb drives, data storage, keyboards, mice, web cams, headsets
- **COMPATIBILITY:** OS independent, works with Windows, macOS, Linux, Chrome OS; Long host cable for USB-A laptops on stands or 2-in-1's (Dell XPS, Microsoft Surface Pro & Laptop, Lenovo ThinkPad X1 Carbon, HP EliteBook, Chromebooks)
- **STARTECH.COM ADVANTAGE:** IT professionals' choice for over 30 years; This expander hub with multiple USB-A ports is backed for 2-years by StarTech.com, including free 24/5 North America based multi-lingual tech support

---


### Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	No
Ports	4
Interface	USB 3.2 Gen 1
Bus Type	USB 3.2 Gen 1 (5 Gbps)
Industry Standards	USB 3.2 - Backward compatible with USB 3.1, 3.0, 2.0 and 1.1
Chipset ID	Realtek - RTS5411E

---

### Performance

Maximum Data Transfer Rate	5Gbps
----------------------------	-------



Type and Rate USB 3.1 Gen 1 - 5 Gbit/s

UASP Support Yes

---

**Connector(s)**

Connector Type(s) USB 3.1 USB Type-A (9 pin, Gen 1, 5 Gbps)

USB 3.1 USB Type-A (9 pin, Gen 1, 5 Gbps)

---

**Software**

OS Compatibility OS Independent

---

**Power**

Power Source Bus Powered

---

**Environmental**

Operating Temperature 0C to 50C (32F to 122F)

Storage Temperature -20C to 70C (-4F to 158F)

Humidity 0% to 95% (non-condensing) at 25C (77F)

---

**Physical Characteristics**

Color Black & Space Gray

Form Factor Compact

Material Plastic

Cable Length 11.0 in [28 cm]

Product Length 5.3 in [13.5 cm]

Product Width 2.0 in [50.0 mm]

Product Height 0.8 in [20.0 mm]

Weight of Product 2.6 oz [75.0 g]

---

**Packaging Information**

Package Length 5.6 in [14.2 cm]

Package Width 6.7 in [17.0 cm]

Package Height 1.2 in [30.0 mm]



Shipping (Package) Weight	4.7 oz [131.9 g]
------------------------------	------------------

---

**What's in the Box**

Included in Package	USB Hub
---------------------	---------

---

***\*Product appearance and specifications are subject to change without notice.***

