

HDMI to DisplayPort Adapter - 4K 30Hz

Product ID: HD2DP



This HDMI to DisplayPort adapter lets you connect an HDMI video source, such as your laptop, desktop, Blu-ray player, or camera, to a DisplayPort monitor or projector.

The active HDMI to DisplayPort adapter offers plug-and-play installation, providing a hassle-free setup with no software or drivers to install. The adapter uses a USB port for power, avoiding the need for an extra power adapter. It also features a compact design that requires very little space at your workstation.

The HDMI to DP adapter lets you add a second monitor to your laptop, providing the additional screen space you need to multitask more efficiently and accomplish more in the same amount of time. It offers a definite productivity boost, and lets you view documents, spreadsheets, and web pages across multiple screens.

With support for 4K at 30Hz, you get a sharp, crisp picture that's richer and more true-to-life than traditional HD, with far greater detail. The adapter delivers Ultra HD content to your DisplayPort monitor and supports 7.1 channel surround audio.

The adapter is backward compatible with 1080p displays, which makes it a great accessory for home, office or other workspace applications.

The HD2DP is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your HDMI computer to a DisplayPort monitor
- View documents, spreadsheets, and web pages across multiple screens
- Design and edit graphic files on your DP display using the HDMI output on your computer
- Edit and view post-production video on a 4K display
- Viewing camera footage from your HDMI source on a DisplayPort monitor

Features

- Provides a compact solution with a plug-and-play installation
- Increase your productivity by connecting a second monitor to your laptop
- Deliver astonishing picture quality with support for video resolutions up to Ultra HD 4K
- Backward compatible with displays supporting Full HD 1920x1200
- Offers USB-powered performance - no drivers or power adapter required

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	HDMI
AV Output	DisplayPort
Audio	Yes
Chipset ID	MegaChips - STDP2600

Performance

Maximum Digital Resolutions	3840 x2160
Supported Resolutions	3840 X 2160 at 30 Hz 1920x1200 1920x1080 (1080p) at 120 Hz 1280x720 (720p)
Wide Screen Supported	Yes
Audio Specifications	7.1 surround sound

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - DisplayPort (20 pin)

Special Notes / Requirements

Note	This adapter does not support HDCP 2.2
------	--

Power

Power Source	USB-Powered
Input Voltage	5V DC
Output Voltage	5 DC

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%-85% RH

Physical Characteristics

Color	Black
Product Length	10.0 in [25.5 cm]
Product Width	0.9 in [2.3 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	2.5 oz [70.0 g]

Packaging Information

Package Quantity	1
Package Length	4.9 in [12.5 cm]
Package Width	5.6 in [14.3 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	4.2 oz [120.0 g]

What's in the Box

Included in Package	1 - HDMI to DisplayPort adapter
	1 - 2ft USB extension cable

****Product appearance and specifications are subject to change without notice.***