

6 in. High Speed HDMI Port Saver Cable - 4K 60Hz

Product ID: HD2MF6INL



This High Speed HDMI port saver cable prevents wear and tear on the HDMI port on your monitor or other devices, by extending it away from the device for a more flexible connection. The port extender cable supports all HDMI 2.0 specifications, including resolutions up to 4K (60Hz), and bandwidth up to 18Gbps.

To prevent accidental disconnections and signal loss, the extender features a high-retention HDMI male connector. The connector automatically latches to the inside of the port, creating contact pressure that prevents it from loosening over time due to movement or vibrations.

This short male-to-female extension cable supports all HDMI 2.0 specifications:

- Resolutions up to 4K 60Hz
- High speeds with a bandwidth of up to 18Gbps
- High Dynamic Range for higher contrast ratio and vivid colors
- Crystal-clear sound with up to 32 uncompressed digital audio channels
- Supports 21:9 cinema aspect ratio and 3D video
- Backward compatible with earlier versions of HDMI
- Supports Consumer Electronics Control (CEC) functions

Fully compatible with your HDMI 2.0 equipment, this port saver cable supports resolutions up to 4K 60Hz and bandwidths up to 18Gbps. It's also backward compatible with earlier versions of HDMI and will work with all of your existing HDMI devices.

HD2MF6INL is backed by a StarTech.com lifetime warranty and free lifetime technical support

Certifications, Reports and Compatibility

Applications

- Deliver high-quality presentations using 4K projectors
- Connect 4K or Ultra HD displays and devices

Features

- Extend your display's HDMI port to prevent wear and tear when connecting to your computer
- Create a secure connection with a connector that grips inside the HDMI port
- Get the best viewing experience supporting all HDMI 2.0 specifications
- Enjoy astonishing picture quality with support for video UHD resolutions up to 4K 60Hz
- Ensure a reliable connection with this high-speed port saver cable

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @ 60hz
-----------------------------	----------------------------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG



Cable Length	6.0 in [15.2 cm]
Product Length	6.0 in [15.2 cm]
Product Width	0.9 in [22.2 mm]
Product Height	0.1 in [3.6 mm]
Weight of Product	0.9 oz [25.0 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.3 in [7.0 mm]
Shipping (Package) Weight	1.1 oz [30.0 g]

What's in the Box

Included in Package	6 in. HDMI Cable
---------------------	------------------

****Product appearance and specifications are subject to change without notice.***

