

6" (15cm) HDMI Port Saver Cable - 4K 60Hz High Speed HDMI 2.0 Extension Cable with Ethernet - Short HDMI Extension Cable - HDMI Male to Female Extension Adapter Cord

Product ID: HD2MF6INL



This High Speed HDMI port saver cable prevents wear and tear on the HDMI port on your monitor or other devices, by extending it away from the device for a more flexible connection. The port extender cable supports all HDMI 2.0 specifications, including resolutions up to 4K (60Hz), and bandwidth up to 18Gbps.

To prevent accidental disconnections and signal loss, the extender features a high-retention HDMI male connector. The connector automatically latches to the inside of the port, creating contact pressure that prevents it from loosening over time due to movement or vibrations.

This male-to-female HDMI extension cable supports all HDMI 2.0 specifications:

- Resolutions up to 4K 60Hz
- High speeds with a bandwidth of up to 18Gbps
- High Dynamic Range (HDR) for higher contrast ratio and vivid colors
- Crystal-clear sound with up to 32 digital audio channels
- Supports 21:9 cinema aspect ratio and 3D video
- Backward compatible with earlier versions of HDMI
- Supports Consumer Electronics Control (CEC) functions

Fully compatible with your HDMI 2.0 equipment, this port saver cable supports resolutions up to 4K 60Hz and bandwidths up to 18Gbps. It's also backward compatible with earlier versions of HDMI and will work with all of your existing HDMI devices.

Certifications, Reports and Compatibility



Applications

- Deliver high-quality presentations using 4K projectors
- Connect 4K or Ultra HD displays and devices

Features

- **EXTENSION CABLE:** 6" (15cm) HDMI 2.0 extension cable with Ethernet, 4K 60Hz (up to 4096x2160p), 18Gbps bandwidth, HDR10 for high contrast ratio, supports Ultra wide aspect ratio, 32 Ch. multi-stream audio w/1536Hz sampling (5.1/7.1/DD+/Dolby TrueHD/Atmos)
- **DURABLE:** Ultra HD high speed fully molded HDMI port saver cable with durable PVC jacket for high strength and reliability; Short HDMI extender cable with flexible PVC strain relief prevents fraying or damage due to repetitive bending or extensive use
- **COMMERCIAL GRADE:** 30AWG wire with gold-plated latching connectors & EMI shielding w/Al-Mylar foil & copper braid (85% coverage) improve signal integrity & reliability; Nylon 6/6 female connector prevents wear & tear when connecting to your HDMI port
- **PREVENT WEAR AND TEAR:** Minimize insertion cycles to protect your HDMI port & allow easier reach; Use with your computer/laptop/desktop/workstation; Connect TV/monitor/display/projector; Ideal for home/office and travel; Samsung/Sony/Apple TV/Dell/LG;
- **SPECS:** 6 inches (15 cm) Black HDMI 2.0 HDMI Male to Female adapter 30 AWG PVC Jacket Shield: Al-Mylar foil with 85% Braid ARC, Deep Color, HDCP 2.2, CEC, BT.2020 colorimetry Supports HDMI 2.0 and earlier Lifetime Warranty

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @ 60hz
-----------------------------	----------------------------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Cable Length	6.0 in [15.2 cm]
Product Length	6.0 in [15.2 cm]
Product Width	0.9 in [2.2 cm]
Product Height	0.1 in [0.4 cm]
Weight of Product	0.9 oz [25.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.3 in [7.0 mm]
Shipping (Package) Weight	1.1 oz [30.0 g]

What's in the Box

Included in Package	1 - 6 in. HDMI Cable
---------------------	----------------------

****Product appearance and specifications are subject to change without notice.***