

1m (3 ft) White CL3 In-wall High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

**Product ID:** HD3MM1MW



The HD3MM1MW 1m (3ft) High Speed HDMI Cable is CL3-Rated for in-wall installations, and features two gold-plated HDMI (male) connectors to provide a dependable high quality HDMI to HDMI connection between devices such as Blu-Ray Disc players, HDTVs, DVD Players, stereo receivers, projectors and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HD3MM1MW 1-meter in-wall HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

## Certifications, Reports and Compatibility

### Applications

- In-wall HDMI cable runs
- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

### Features

- 2x HDMI Male Connectors
- CL3 cable rating
- Supports Ultra HD Resolutions up to 4k x 2k
- Gold-plated HDMI connectors
- High quality construction

---

### Prominence

Warranty	Lifetime
Description CDW 75 - 1st Line	StarTech.com 3ft 1m Certified High Speed HDMI 1.4 Cable CL3 In-wall 4K x 2K

---

### Hardware

Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CL3 Rated

---

### Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

---

### Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

---

### Physical Characteristics

Color	White
Connector Style	Straight
Wire Gauge	30/32 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100 cm]
Product Width	0.8 in [20.5 mm]



Product Height 0.4 in [11 mm]

Weight of Product 1.6 oz [44 g]

---

**Packaging Information**

Package Quantity 1

Package Length 8.7 in [22 cm]

Package Width 7.9 in [20 cm]

Package Height 0.9 in [22 mm]

Shipping (Package) Weight 1.9 oz [54.2 g]

---

**What's in the Box**

Included in Package 1m White CL3 High Speed HDMI Cable - M/M

---

***\*Product appearance and specifications are subject to change without notice.***

