

3ft (1m) Mini HDMI to DVI Cable - DVI-D to HDMI Cable (1920x1200p) - 19 Pin HDMI Mini Male to DVI-D Male - Digital Monitor Cable Adapter M/M - Mini HDMI to DVI Adapter

Produkt ID: HDCDVIMM1M



The HDCDVIMM1M 1m Mini HDMI® to DVI-D Cable enables you to view your pictures and videos from your HDMI Mini-equipped camera or other mobile device (Tablet, laptop, etc.) on a DVI-D capable display or projector. As an option, in order to incorporate audio with your video presentations you can use our 3ft (1m) Slim 3.5mm Stereo Audio Cable (MU3MMS).

Backed by Lifetime Warranty, the HDCDVIMM1M is designed and constructed for maximum durability, to ensure dependable performance.

Certifikat, rapporter och kompatibilitet



Användning

- Connect your HDMI Mini-equipped camera or other mobile device (Tablet, laptop, etc.) to a DVI-D display or projector

Funktioner

- MINI HDMI TO DVI CABLE: 3.3 ft (1 m) Mini HDMI male to DVI-Digital (19-pin) male cable supports

Full HD 1920x1200p, 60Hz/1080p, Single link, 3.9 Gbps bandwidth, 24 Bpp (RGB) color depth

- **DURABLE:** Full HD high speed fully molded cable with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** 30AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** This cable connects Mini HDMI (Type-C) devices such as phones, tablets, laptops and cameras (DSLR/Video) to your DVI-Digital monitor/DVI display/projector; Ideal for viewing on larger screens; works with Samsung/Dell/HP/Acer/LG monitors
- **SPECIFIKATIONER:** 1 m | Svart | HDMI-hane (HDMI Type-C/Mini) till DVI-Digital (19-stift) hane | Guldpläterade kontakter | 30 AWG | 5 mm OD | PVC-hölje | EMI-skydd: Aluminiummylarfolie med kopparflätning

Hårdvara

Garantipolicy	Lifetime
Active or Passive Adapter	Passiv
Kontaktplätering	Guld
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Kontakt(er)

Connector A	1 - Mini HDMI (19-stifts)
Connector B	1 - DVI-D (19-stifts)

Utseende

Färg	Svart
Kontakttyp	Rak
Tråddimension	30 AWG
Kabellängd	3.3 ft [1 m]
Produktlängd	39.4 in [100.0 cm]
Produktbredd	1.6 in [4 cm]

	Produkthöjd	0.4 in [1 cm]
	Produktvikt	2.4 oz [68.0 g]
Förpackning	Förpackningsantal	1
	Paketets längd	7.1 in [18.1 cm]
	Paketets bredd	7.8 in [19.8 cm]
	Paketets höjd	0.9 in [2.2 cm]
	Fraktvikt (förpackning)	2.7 oz [76.0 g]
Vad det är i lådan	Ingår i paketet	1 - 1m Mini HDMI® to DVI-D Cable - M/M
Warranty Information	Warranty	Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.