

3m Micro HDMI to HDMI Cable with Ethernet - 4K 30Hz Video - Durable High Speed Micro HDMI Type-D to HDMI 1.4 Adapter Cable/Converter Cord - UHD HDMI Monitors/TVs/Displays - M/M

Product ID: HDADMM3M



The HDADMM3M High Speed Cable with Ethernet (3m) features one HDMI (A) male connector and one HDMI Micro (D) connector, enabling you to connect devices with an HDMI Micro port to a display/device with a standard HDMI port - a cost-saving solution for connecting cutting-edge and next-generation HDMI-capable devices to existing HDMI technology.

The HDMI/HDMI Micro cable features high-quality gold-tipped connectors that ensure peak connectivity, and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your smartphone or other HDMI Micro-equipped portable device to your HDMI-enabled TV or display

Features

- **HIGH SPEED MICRO HDMI to HDMI CABLE:** 3m HDMI 1.4b adapter cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** Ultra HD high speed fully molded Micro HDMI to HDMI converter cable w/ durable PVC jacket for high

strength/reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending/rough usage; Ideal for commercial environment

- **QUALITY CONSTRUCTION:** Micro HDMI to HDMI video cord constructed with 32AWG wire & gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** This adapter connects Micro HDMI (Type-D) devices such as phones, tablets, laptops and cameras (DSLR/Video) to your HDMI (Type-A) TV, monitor, display, projector; Ideal for viewing on larger screens; Samsung/Sony/Apple TV/Dell/LG
- **SPECS:** 3 m Black HDMI 1.4b HDMI Male (Type-D/Micro) to HDMI Male (Type-A/Standard) 32 AWG PVC Jacket Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier Lifetime Warranty

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - Micro HDMI (19 pin)

Physical Characteristics

Color	Black
Wire Gauge	32 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	3.0 oz [85.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.5 in [1.2 cm]
Shipping (Package) Weight	3.3 oz [94.0 g]

What's in the Box

Included in Package	1 - 3m High Speed HDMI Cable with Ethernet - HDMI to HDMI Micro - M/M
---------------------	---

****Product appearance and specifications are subject to change without notice.***